





REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASE NEW DWG FORMAT	Sep-30-2019	Flan	Tommy



- NOTES: (UNLESS OTHERWISE SPECIFIED)
- MATERIAL: COPPER ALLOY, SILVER PLATED
 - SPECIFICATIONS:
 - RATED CURRENT: 45 A(MAX)
 - TERMINATION TYPE: CRIMPING
 - AVAILABLE WIRE RANGE: 2(8AWG) TO 2(10MM)
 - RoHS COMPLIANT
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SECTION A-A



	SEE PART NUMBER CHART		
QUANTITY	PART NUMBER	DESCRIPTION	
MATERIALS LIST			
<div>UNLESS OTHERWISE SPECIFIED: 1) All dimensions are in mm (mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.00 <div>3) Hole reference = </div></div>		<div>SIGNATURES</div> <div>DATE</div> <div>DRAWN: Flan Sep-30-2019</div> <div>CHECKED: Mark Sep-30-2019</div> <div>ENGINEER:</div> <div>APPROVAL: Tommy Sep-30-2019</div>	<div>Amphenol</div> <div>Sine Systems – www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036</div>
MATERIAL SPECIFICATIONS:		Socket Contact with RADSOK® Technology. Crimp Barrel, Size 8 (3.6mm), Wire Range 10mm², 8AWG	
PROCESS SPECIFICATIONS:		SIZE TYPE DWG NO: REVISION	
NEXT ASS'Y:		B C – MISCARS3S-10 B1	
		SCALE: 2 : 1 SHEET 11 OF	

TITLE:	DWG NO:	REV:	SH:	OF:
	MISCARS3S-10	D1	1	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS6ARS8S-10](#)