






REV	SIGN	DATE	DESCRIPTION	APPROVER
A0		2021.11.19	Initial release	
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



Material

- Item ① Start Housing: Thermoplastic (UL 94V-0)
- Item ② Fornt housing: Thermoplastic (UL 94V-0)
- Item ③ Back housing: Thermoplastic (UL 94V-0)
- Item ④ End cover: Thermoplastic (UL 94V-0)
- Item ⑤ cage: Stainless steel
- Item ⑥ Back pin : Copper ,plating Sn over Nickel.
- Item ⑦ fornt pin : Copper ,plating Sn over Nickel
- Item ⑧ Lever : Thermoplastic Grey(RAL7004/P)(UL 94V-0)
- Item ⑨ Spring : Stainless steel
- Electrical : cULus / TUV(EN/IEC 60947-7-4)
- Voltage rating: 600V / 800V (III/3) 1000V(III/2) 1000V(III/2)
- Current rating: 30A / 41A
- Wire range: 0.2-6mm²
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 10-24
- Wire strip length: 10.5mm
- Withstanding Voltage: 2.2KV / 4.2KV
- Rated impulse Withstanding Voltage: 8KV
- Operating temperature: -40°C to +115°C
- Safety approval:
- Critical dimension:
- The device must be powered-off while the user insert or remove conductors

No. OF POLES		N6 XX 30 X 0 XXXX G	RoHS compliant
02 2 CONTACTS	Body Color	0 Black (RAL9005)	
...		2 Red (RAL3001/D)	
20 20 CONTACTS		3 Orange(RAL2011/P)	
		4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7004/P)	
		9 White(RAL1102)	
		C Multiple colors	


0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

DIM	P	2	3	4	5	6	7	8	9	10	16.50
	L	14.1	20.45	26.8	33.15	39.5	45.85	52.2	58.55	64.9	
	A	6.35	12.7	19.05	25.4	31.75	38.1	44.45	50.8	57.15	
	TOL	±0.25					±0.35				
DIM	P	11	12	13	14	15	16	17	18	19	20
	L	71.25	77.6	83.95	90.3	96.65	103.0	109.35	115.7	122.05	128.4
	A	63.5	69.85	76.2	82.55	88.9	95.25	101.6	107.95	114.3	120.65
	TOL	±0.45					±0.55				

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		N6 6.35mm Series Spring-cage terminal block								
PART NO.		N6xx30x0xxxxG			DWG NO.	8N60001				
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Rhine 2021.11.19		Rhine 2021.11.19				UNIT: mm	X.	±0.50
								SCALE: 1:1	X.X	±0.30
						SHEET: 01/01	REV.: A0	X.XX	±0.10	
								X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[N60330000000G](#) [N60330500000G](#) [N60430000000G](#) [N60430500000G](#) [N60530000000G](#) [N60530500000G](#)