



- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- 3D model search
- Customer drawing search
- Free search
- Search by category
- E-Services
- Distributor list

Start > Search=61729-1010R* > 61729-1010RLF

61729-1010RLF

61729-1010RLF - USB : Type B, Receptacle, Through Hole, 30u GXT Contact, 4 Pins, Full Back Shield with Bright Tin Plating, 1.57 mm PCB, Black HSG, Tape and Reel packing

ACTIVE

RoHS Compliant

Customer drawing

Environmental Compliance Report

Specifications

Download document

Approvals / Certifications

Dimensional

General

Mounting

Physical

Other Features

Approvals / Certifications

USB 2.0 Qualified	Yes
USB 3.0 Qualified	No

Dimensional

Thickness (Board - recommended)	1.57 mm
Thickness (Panel - max)	2.67 mm

General

Add to Favorites

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

portal.fciconnect.com/portal/page/portal/fciconnect/ecatalog?apname=catDisplayStyle\$domProductQ...

1/2

Hold Down Style	Standard
Number of contacts	4
Orientation	Right Angle
Pin Orientation	Standard
Product Type	Receptacle
Shell Options	Back Shield
Style	B Type
Sensor Contact Options	without Sensor Contact
Series Number	61729
Single or Dual Stack	Single
Mounting	
Mounting flange / Hole options	None
Mounting style	Through Hole
Physical	
Color (Housing)	Black
Material (Housing)	Glass - Fiber Filled Thermoplastic, UL 94V-0
Plating (Contact area)	30u" GXT
Plating (Shell)	Pure Tin / Nickel Under Plating
Plating (Tail)	100u" Pure Tin
Other Features	
Most Popular Configuration	Not Applicable
Packaging (Options)	Tape and Reel

FCI copyrights 2007 - 2012 All rights reserved for all countries - Privacy Policy

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[61729-1010RLF](#)