


1234567





SIGN	DATE	DESCRIPTION	APPROVER
△	2011.08.24	The dimension is changed from 15.24mm to 15.00±0.20mm	Aaron
△	2011.08.24	The dimension are added	Aaron
△	2011.08.24	The dimension is changed from 15.24mm to 15.00mm	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Short male Contact pin: Copper ,Tin plated
- Item ② Long male Contact pin: Copper ,Tin plated
- Item ③ Terminal (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 
- Critical dimension: ▽



VF xx 70 x 0 xxxx G

Poles	Color	RoHS
04 2×2Poles	0 Black (RAL9005)	Pb<40,000ppm
06 2×3Poles	2 Red (RAL3001/D)	0000 Standard @ Logo
...	3 Orange(RAL2011/P)	000A Standard ANY Logo
48 2×24Poles	4 Yellow(RAL1018/A)	Any special item by customer request, please contact sales department.
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	


N=NUMBER OF CONTACTS

Dimension		TOL				
		2×2P-2×5P	2×6P-2×10P	2×11P-2×15P	2×16P-2×20P	2×21P-2×24P
Dim L	N/2×5.0	±0.15	±0.20	±0.25	±0.30	±0.35
Dim B	(N/2-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.35
Dim C	(N/2-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.35
Dim D	(N/2-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.35

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VF-5.00 Series 2×2P-2×24P (Open) Vertical				
PART NO.	VFxx70x0xxxxG		DWG NO.	8VF0004	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Aaron 2011.08.24	Chen Bo 2011.02.21		X. ±0.50
				UNIT: mm	X.X ±0.30
				SCALE: NONE	X.XX ±0.10
				SHEET: 01/01	X° ±1°
				REV.: C	

1234567

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VF0470500000G</u>	<u>VF0670500000G</u>	<u>VF0870500000G</u>	<u>VF1070500000G</u>	<u>VF1270500000G</u>	<u>VF1470500000G</u>
<u>VF1670500000G</u>	<u>VF1870500000G</u>	<u>VF2070500000G</u>	<u>VF2270500000G</u>	<u>VF2470500000G</u>	<u>VF2670500000G</u>
<u>VF2870500000G</u>	<u>VF3070500000G</u>	<u>VF3270500000G</u>	<u>VF3470500000G</u>	<u>VF3670500000G</u>	<u>VF3870500000G</u>
<u>VF4070500000G</u>	<u>VF4270500000G</u>	<u>VF4470500000G</u>	<u>VF4670500000G</u>	<u>VF4870500000G</u>	