






1	2	3	4	5	6	7																																																																																																								
				<table><tr><td>SIGN</td><td>DATE</td><td>DESCRIPTION</td><td>APPROVER</td></tr><tr><td>△</td><td>10/28'08</td><td>The temperature changed from -40°C to +115°C</td><td>Kind</td></tr><tr><td colspan="4">THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</td></tr></table>			SIGN	DATE	DESCRIPTION	APPROVER	△	10/28'08	The temperature changed from -40°C to +115°C	Kind	THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																																																															
				SIGN	DATE	DESCRIPTION	APPROVER																																																																																																							
				△	10/28'08	The temperature changed from -40°C to +115°C	Kind																																																																																																							
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																																																																														
<p>Material</p> <ul style="list-style-type: none">● Item① Male contact pin: Brass(CuZn),Tin or Au plated.● Item② Terminal (housing): Thermoplastic (UL94V-0) <p>Electrical</p> <ul style="list-style-type: none">● Voltage rating: 300V● Current rating: 10A● Withstanding Voltage: 1.6KV△ Operating temperature: -40°C to +115°C● Soldering temperature: 250°C±10°C/5 Sec● Safety Approval: 																																																																																																														
																																																																																																														
																																																																																																														
																																																																																																														
				<p>EX xx 0 x x 0 xxxx G</p> <div><div>02 2 CONTACTS 0 Tin plating</div><div>03 3 CONTACTS 1 G/F plating</div><div>... ..</div><div>24 24 CONTACTS</div></div> <div><div>0 Black (RAL9005)</div><div>2 Red (RAL3001/D)</div><div>3 Orange(RAL2011/P)</div><div>4 Yellow(RAL1018/A)</div><div>5 Green(RAL6018/T)</div><div>6 Blue (RAL5015/A)</div><div>8 Grey(RAL7035/D)</div></div> <div><div>000 0 Standard</div><div>Any special item by customer request, please contact sales department.</div><div>Pb < 40,000ppm (RoHS)</div></div>																																																																																																										
<table><tr><td>Poles</td><td>02</td><td>03</td><td>04</td><td>05</td><td>06</td><td>07</td><td>08</td><td>09</td><td>10</td><td>11</td><td>12</td><td>13</td></tr><tr><td>Dim L</td><td>12.7</td><td>17.7</td><td>22.7</td><td>27.7</td><td>32.7</td><td>37.7</td><td>42.7</td><td>47.7</td><td>52.7</td><td>57.7</td><td>62.7</td><td>67.7</td></tr><tr><td>Dim B</td><td>5.00</td><td>10.00</td><td>15.00</td><td>20.00</td><td>25.00</td><td>30.00</td><td>35.00</td><td>40.00</td><td>45.00</td><td>50.00</td><td>55.00</td><td>60.00</td></tr><tr><td>TOL</td><td colspan="5">±0.15</td><td colspan="5">±0.20</td><td colspan="2">±0.25</td></tr><tr><td>Poles</td><td>14</td><td>15</td><td>16</td><td>17</td><td>18</td><td>19</td><td>20</td><td>21</td><td>22</td><td>23</td><td>24</td><td></td></tr><tr><td>Dim L</td><td>72.7</td><td>77.7</td><td>82.7</td><td>87.7</td><td>92.7</td><td>97.7</td><td>102.7</td><td>107.7</td><td>112.7</td><td>117.7</td><td>122.7</td><td></td></tr><tr><td>Dim B</td><td>65.00</td><td>70.00</td><td>75.00</td><td>80.00</td><td>85.00</td><td>90.00</td><td>95.00</td><td>100.0</td><td>105.0</td><td>110.0</td><td>115.0</td><td></td></tr><tr><td>TOL</td><td colspan="5">±0.25</td><td colspan="5">±0.30</td><td colspan="2"></td></tr></table>				Poles	02	03	04	05	06	07	08	09	10	11	12	13	Dim L	12.7	17.7	22.7	27.7	32.7	37.7	42.7	47.7	52.7	57.7	62.7	67.7	Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	TOL	±0.15					±0.20					±0.25		Poles	14	15	16	17	18	19	20	21	22	23	24		Dim L	72.7	77.7	82.7	87.7	92.7	97.7	102.7	107.7	112.7	117.7	122.7		Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0		TOL	±0.25					±0.30									
Poles	02	03	04	05	06	07	08	09	10	11	12	13																																																																																																		
Dim L	12.7	17.7	22.7	27.7	32.7	37.7	42.7	47.7	52.7	57.7	62.7	67.7																																																																																																		
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00																																																																																																		
TOL	±0.15					±0.20					±0.25																																																																																																			
Poles	14	15	16	17	18	19	20	21	22	23	24																																																																																																			
Dim L	72.7	77.7	82.7	87.7	92.7	97.7	102.7	107.7	112.7	117.7	122.7																																																																																																			
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0																																																																																																			
TOL	±0.25					±0.30																																																																																																								
				<table><tr><td colspan="2">TITLE</td><td colspan="2">EX 5.0 Series 2P-24P</td></tr><tr><td colspan="2">PART NO.</td><td colspan="2">EXxx0xx0xxxxG</td></tr><tr><td colspan="2">DWG NO.</td><td colspan="2">8EX0001</td></tr><tr><td colspan="2">APPROVED</td><td colspan="2">CHECKED</td></tr><tr><td colspan="2">DESIGNED</td><td colspan="2">DRAWN</td></tr><tr><td colspan="2">CUST NO.</td><td colspan="2">Tolerance</td></tr><tr><td colspan="2">Kind 2008.10.28</td><td colspan="2">Kind 2008.10.28</td></tr><tr><td colspan="2">SHEET: 01/01</td><td colspan="2">UNIT: mm</td></tr><tr><td colspan="2"></td><td colspan="2">SCALE: NONE</td></tr><tr><td colspan="2"></td><td colspan="2">REV.: C</td></tr></table>			TITLE		EX 5.0 Series 2P-24P		PART NO.		EXxx0xx0xxxxG		DWG NO.		8EX0001		APPROVED		CHECKED		DESIGNED		DRAWN		CUST NO.		Tolerance		Kind 2008.10.28		Kind 2008.10.28		SHEET: 01/01		UNIT: mm				SCALE: NONE				REV.: C																																																																	
TITLE		EX 5.0 Series 2P-24P																																																																																																												
PART NO.		EXxx0xx0xxxxG																																																																																																												
DWG NO.		8EX0001																																																																																																												
APPROVED		CHECKED																																																																																																												
DESIGNED		DRAWN																																																																																																												
CUST NO.		Tolerance																																																																																																												
Kind 2008.10.28		Kind 2008.10.28																																																																																																												
SHEET: 01/01		UNIT: mm																																																																																																												
		SCALE: NONE																																																																																																												
		REV.: C																																																																																																												
1	2	3	4	5	6	7																																																																																																								

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>EX0200000000G</u>	<u>EX0300000000G</u>	<u>EX0400000000G</u>	<u>EX0500000000G</u>	<u>EX0600000000G</u>	<u>EX0700000000G</u>
<u>EX0800000000G</u>	<u>EX0900000000G</u>	<u>EX1000000000G</u>	<u>EX1100000000G</u>	<u>EX1200000000G</u>	<u>EX1300000000G</u>
<u>EX1400000000G</u>	<u>EX1500000000G</u>	<u>EX1600000000G</u>	<u>EX1700000000G</u>	<u>EX1800000000G</u>	<u>EX1900000000G</u>
<u>EX2000000000G</u>	<u>EX2100000000G</u>	<u>EX2200000000G</u>	<u>EX2300000000G</u>	<u>EX2400000000G</u>	