





N = Number of poles
Dim A=Nx5.0+0.50
Dim B=(N-1)x5.0

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.25	±0.25
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	11.01'05	Standard spec is changed.	Marivn
△	8/07'06	Added VDE and TUV standard	梁仁松
△	12/02'08	With flange screw changed from "-" slot type to "+/-" slot type	Jacke
△	12/02'08	The temperature changed from -30°C +105°C to -40°C +115°C	Jacke
△	12/02'08	Add the tolerance table	Jacke
△	2010.03.13	Add the 2p mark	Jacke
△	2010.05.28	The design is changed	Chen Bo
△	2010.08.16	The design is changed	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating "-" slot type
- Item c Female contact: PhBz Tin plated
- Item d Terminal (up body): Thermoplastic (UL94V-0)
- Item e Terminal (down body): Thermoplastic (UL94V-0)
- △ Item f With flange screw: Steel Zinc plating "+/-" slot type M2.5
- △ △ Electrical cULus/VDE/TUV
 - Voltage rating: 300VAC/300VAC/300VAC
 - Current rating: 15A/17A/15A
 - Wire range: 2.5mm² /0.34-2.5mm²
 - Solid wire(AWG): 12-24
 - Stranded wire(AWG): 12-24
 - Torque: 3.5Lb-In./0.5Nm/0.4Nm
 - Screw: M3
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV/2.5KV/2.5KV
 - △ Operating temperature: -40°C to +115°C
 - Safety approval:   

TS xx 71 x C xxxx G

02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

RoHS
Pb<40,000ppm
0000: "@" Logo
000A: "ANYTEK" Mark
0091: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TS-5.0mm Series(W/latching hooks on the wire entry side) with flange							
PART NO.	TSxx71xCxxxxG			DWG NO.	8TS0003				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
			Chen Bo 2010.08.16		UNIT: mm		X. ±0.50		
					SCALE: NONE		X.X ±0.30		
					REV: I		X.XX ±0.10		
SHEET: 01/01				REV: I		X° ±1°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TS02715C0000G</u>	<u>TS03715C0000G</u>	<u>TS04715C0000G</u>	<u>TS05715C0000G</u>	<u>TS06715C0000G</u>	<u>TS07715C0000G</u>
<u>TS08715C0000G</u>	<u>TS09715C0000G</u>	<u>TS10715C0000G</u>	<u>TS11715C0000G</u>	<u>TS12715C0000G</u>	<u>TS13715C0000G</u>
<u>TS14715C0000G</u>	<u>TS15715C0000G</u>	<u>TS16715C0000G</u>	<u>TS17715C0000G</u>	<u>TS18715C0000G</u>	<u>TS19715C0000G</u>
<u>TS20715C0000G</u>	<u>TS21715C0000G</u>	<u>TS22715C0000G</u>	<u>TS23715C0000G</u>	<u>TS24715C0000G</u>	<u>TS07718C0000G</u>
<u>TS02718C0000G</u>	<u>TS16718C0000G</u>	<u>TS06718C0000G</u>	<u>TS09718C0000G</u>	<u>TS14718C0000G</u>	<u>TS22718C0000G</u>
<u>TS11718C0000G</u>	<u>TS12710C0000G</u>	<u>TS15718C0000G</u>	<u>TS17718C0000G</u>	<u>TS18710C0000G</u>	<u>TS20710C0000G</u>
<u>TS21710C0000G</u>	<u>TS24710C0000G</u>	<u>TS09710C0000G</u>	<u>TS10710C0000G</u>	<u>TS14710C0000G</u>	<u>TS15710C0000G</u>
<u>TS22710C0000G</u>	<u>TS17710C0000G</u>	<u>TS21718C0000G</u>	<u>TS23710C0000G</u>	<u>TS19718C0000G</u>	<u>TS23718C0000G</u>
<u>TS13718C0000G</u>	<u>TS18718C0000G</u>	<u>TS08718C0000G</u>	<u>TS24718C0000G</u>	<u>TS19710C0000G</u>	<u>TS20718C0000G</u>
<u>TS04710C0000G</u>	<u>TS10718C0000G</u>	<u>TS16710C0000G</u>	<u>TS07710C0000G</u>	<u>TS11710C0000G</u>	<u>TS13710C0000G</u>
<u>TS03710C0000G</u>	<u>TS08710C0000G</u>	<u>TS03718C0000G</u>	<u>TS04718C0000G</u>	<u>TS06710C0000G</u>	<u>TS02710C0000G</u>
<u>TS05718C0000G</u>	<u>TS12718C0000G</u>	<u>TS05710C0000G</u>			