



REVISIONS					
REV	ZONE	ECO	DESCRIPTION	DATE	BY APPR
A	-	-	-	-	-

P28820
XM-MM/DD/YY

MM: MONTH
DD: DAY
YY: YEAR




P1





P2


P3




WIRING DIAGRAM



FEMALE 4 PIN INTERNAL THREAD
FACE VIEW



FEMALE 5 PIN DEVCENET
INTERNAL THREAD
FACE VIEW



MALE 9 PIN
FACE VIEW

PART NUMBER		DESCRIPTION		ITEM
P28820		CONTROLBOSS ADAPTER, 120VAC FEMALE TAP		A
QUANTITY		MATERIALS LIST		
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE
1) All dimensions are in inches.		DRAWN: C. LOPKOCIO		8/3/07
2) Tolerances are as follows:		CHECKED:		
1 PL DEC ±0.05		FRACTIONS ±1/64		
3 PL DEC ±0.01		ANGLES ±1°		
3) Fabrication Standards Per:		ENGINEER: C. LOPKOCIO		
SS-20020		APPROVAL:		
4) Note Reference = A		CUSTOMER:		
MATERIAL SPECIFICATIONS:		THE USE OF THIS DOCUMENT IS UNLIMITED. DESIGN FEATURES, SPECIFICATIONS, AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF AMPHENOL SINE SYSTEMS. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. MAY CONTAIN LIMITED RIGHTS DATA.		
PROCESS SPECIFICATIONS:		SIZE: FSQM NO. DWG NO:		REVISION
IPC/WHMA-A-620		C 10K44		P28820 A
NEXT ASSY:		C-P28820		
		SHEET 1 OF 1		

TITLE:

CONTROLBOSS ADAPTER, 120VAC

DWG NO:

P28820

REV: A

SH: 1

OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[P28820](#)