



| REVISIONS |     |                              |           |     |      |
|-----------|-----|------------------------------|-----------|-----|------|
| REV       | ECO | DESCRIPTION                  | DATE      | BY  | APPR |
|           |     | TECHNICAL DATA SHEET RELEASE | 12-MAY-14 | KMM | RFC  |



#### TECHNICAL DATA:

- 1) MATERIALS:  
 COUPLING NUT: MACHINED ALUMINUM, ANODIZED  
 INSULATION INSERT: THERMOPLASTIC, UL 94/V-0  
 CONTACT: GOLD FLASH PLATING OVER COPPER ALLOY  
 OVERMOLD MATERIAL: THERMOPLASTIC COLOR: BLACK  
 CABLE RATING: UL LISTED DUAL RATED TC-ER/STOOW,  
 CSA TYPE STOOW, FT4 FLAME RATING, 600V,  
 90°C DRY & 75°C WET (TC-ER), 105°C (STOOW)  
 CABLE JACKET MATERIAL: PVC COLOR: BLACK  
 CONDUCTOR INSULATION: PVC  
 NUMBER OF CONDUCTORS: (4) 14AWG

- 2) ELECTRICAL DATA:  
 CURRENT (MAX): 15A  
 VOLTAGE (MAX): 600V AC/DC  
 INSULATION RESISTANCE (MIN): 5000M OHMS  
 DIELECTRIC TEST VOLTAGE: 2200V

- 3) MECHANICAL DATA:  
 TEMPERATURE RANGE: -40°C TO 90°C  
 PROTECTION: IP67 (MATED CONDITION)  
 MATING CYCLES: >500  
 VIBRATION RESISTANCE PER MIL-STD-202 METHOD 204  
 THERMAL SHOCK PER MIL-STD-202 METHOD 207  
 48 HOUR SALT SPRAY PER MIL-STD-202 METHOD 101

- 4) RoHS COMPLIANT  
 5) UL 2237 LISTED ASSEMBLY  
 UL FILE NUMBERS: E339703

| Amphenol P/N | ROCKWELL P/N     | MOLEX         | TURCK      |
|--------------|------------------|---------------|------------|
| P29018-M*    | 280-PWRM24E-M*   | 104000A46M*   | RKM44-*M   |
| P29018-M1    | 280-PWRM24E-M010 | 104000A46M010 | RKM44-010M |
| P29018-M2    | 280-PWRM24E-M020 | 104000A46M020 | RKM44-020M |
| P29018-M3    | 280-PWRM24E-M030 | 104000A46M030 | RKM44-030M |
| P29018-M5    | 280-PWRM24E-M050 | 104000A46M050 | RKM44-050M |
| P29018-M10   | 280-PWRM24E-M100 | 104000A46M100 | RKM44-100M |

| TOLERANCE                  |                             |
|----------------------------|-----------------------------|
| 0-2.99 M = +100.0/-25.0mm  | 0-9.99 FT = +4" / -1"       |
| 3-8.99 M = +150.0/-25.0mm  | 10.00-29.99 FT = +6" / -1"  |
| 9-14.99 M = +300.0/-25.0mm | 30.00-49.99 FT = +12" / -1" |
| 15-OVER M = +450.0/-25.0mm | 50 FT-OVER = +18" / -1"     |

|                                                                                                                                                                                                                  |  |                                                                                                                                                                                                                                                                      |             |          |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------|
| PART NUMBER                                                                                                                                                                                                      |  | DESCRIPTION                                                                                                                                                                                                                                                          |             | ITEM     |
| QUANTITY                                                                                                                                                                                                         |  | MATERIALS LIST                                                                                                                                                                                                                                                       |             |          |
| UNLESS OTHERWISE SPECIFIED<br>1) All dimensions are in metric (mm).<br>2) Tolerances are as follows:<br>1 PL DEC ±0.30   Fractions ±1/64<br>2 PL DEC ±0.15   Angles ±1°<br>3 PL DEC ±0.08<br>3) Note reference = |  | SIGNATURES    DATE<br>DRAWN: KMM    12-MAY-14<br>CHECKED: MRF    12-MAY-14<br>ENGINEER: KMM<br>APPROVAL: RFC    12-MAY-14<br>CUSTOMER:                                                                                                                               |             |          |
| MATERIAL SPECIFICATIONS:                                                                                                                                                                                         |  | <br>Sine Systems - www.amphenol-sine.com<br>44724 Morley Drive<br>Clinton Township, MI 48036                                                                                                                                                                         |             |          |
| PROCESS SPECIFICATIONS:                                                                                                                                                                                          |  | THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. |             |          |
| NEXT ASSY:                                                                                                                                                                                                       |  | SIZE                                                                                                                                                                                                                                                                 | TYPE        | DWG NO.  |
|                                                                                                                                                                                                                  |  | C-                                                                                                                                                                                                                                                                   | P29018-Mxxx | A1       |
|                                                                                                                                                                                                                  |  | SCALE                                                                                                                                                                                                                                                                | FULL        | C-P29018 |
|                                                                                                                                                                                                                  |  | SHEET                                                                                                                                                                                                                                                                | 1           | OF 1     |

TYPED: PB LITE, 4 PIN, F-STR, 14AWG, TC-ER/STOOW, P/N dws no: C-P29018-Mxxx  
 REV: A1  
 SR: 1  
 OF: 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[P29018-M2](#)