






PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family LATCH-N-LOK			
ltr ecn nodr date				tolerances unless otherwise specified						title			
H	ELX-N-008457	ZK	11/28/11	angles	linea	.XX±.01/0.X±0.3		INCH/MM		2X10 LNL LOW PROFILE RT. ANGLE HEADER ASSEMBLY			
C	V10987	TFG	3/1/01	0°±2°		.XXX±.005/0.XXX±0.13		scale 1:1					
D	M05-0062	ERE	4/01/05	dr	M. CORNMANN	10/29/90				dwg no		sheet 1 of 2	size
E	M06-0285	AGS	7/28/06	engr	D. HORCHLER	10/29/90				79610		A3	
F	M06-0365	AGS	9/20/06	chr	D. HORCHLER	10/29/90							
G	M09-0048	MHT	3/12/09	appd	D. HORCHLER	10/29/90				type Product Customer Drawing			
sheet revision				H	H								
index sheet				1	2								

PDS: Rev :H

STATUS: Released

Printed: Sep 11, 2013




LEAD FREE OPTION ⑥⑦

	COLOR ④	
1	70343 LT GRAY	OBS
2	80166 OFF WHITE	
3	70634 DK GRAY	OBS
4	701 BLACK	
5	70511 SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING ③
0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni



PIN LENGTH	
	DIM L
0	.200/5.08
1	.130/3.30



RECOMMENDED PCB LAYOUT

NOTES:

1. HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC,
UL-94V-0 RATED.
2. GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u TIN.
- ③ SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING OPTION: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
- ④ NUMBERS SHOWN ARE FOR G.E. LEXAN
AND ARE FOR REFERENCE ONLY.
5. THIS ASSEMBLY UL APPROVED PER FILE E66906 VOL 1, SEC. 84
AND CSA APPROVED PER MASTER FILE LR 46923. PACKAGING
- ⑥ ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
9. PRODUCT SPEC: GS-12-003

mat'l. code			surface <input checked="" type="checkbox"/> tolerance <input type="checkbox"/>		projection <input type="checkbox"/>		product family	
			ISO 1302 <input checked="" type="checkbox"/> ISO 406 <input type="checkbox"/> ISO 1101 <input type="checkbox"/>				LATCH-N-LOK	
ltr ecn nodr date			tolerances unless otherwise specified			title		
H			angles		INCH/MM		2X10 LNL LOW PROFILE RT.	
			linea				ANGLE HEADER ASSEMBLY	
			0°±2'		scale 1:1			
			dr M. CORNMAN 10/29/90				dwg no sheet2 of 2 size	
			engr D. HORCHLER 10/29/90				79610 A3	
			chr D. HORCHLER 10/29/90					
			app D. HORCHLER 10/29/90					
sheet revision							type Product Customer Drawing	
index sheet								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[79610-001LF](#)