











FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE					
ltr ecn no dr date				tolerances unless otherwise specified						title					
M V10994 DLW 3/9/01				angles		linear		.XX±.01/0.3		INCH/MM scale 4:1					
N V11674 CRG 6/22/01						.XXX±.005/0.13									
P M05-0123 ERE 6/10/05				0°±2°		.XXXX±.0020/0.051									
R M06-0225 ERE 6/12/06				dr		M. CORNMANN		7/22/91							
S M06-0370 MHT 9/26/06				engr		M. HAHN		7/22/91							
T M09-0058 CMR 4/06/09				chr		M. HAHN		7/22/91							
U ELX-N-010207 YO 2/8/12				appd		M. HAHN		7/22/91							
sheet index		revision		U		U				dwg no		sheet 1 of 2		size	
		sheet		1		2				87814				A3	
										type		Product		Customer Drawing	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[87814-610LF](#)