



Copyright FCI.










spec ref		dr		Nickor Zuo	2014/02/04	projection		MM		size	A3	scale	7:5		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Nickor Zuo					2014/03/27	ecn no	ELX-DG-17300-1			
				chr	-					-	rel level			Released	
		appr		Collins Lu	2014/03/27	product family			-						
surface		linear	0.X	±0.30		title	DDR4 288Pin DIMM CONNECTOR				dwg no	10129040		rev	B
			0.XX	±0.20											
			0.XXX	±0.10											
	ISO 1302		angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw				sheet 1 of 5		

Copyright FCI.





DDR4 MODULE
MORE INFORMATION REFER TO JEDEX MO-309



spec ref	dr	2014/02/04	projection	MM	size	A3	scale	1:1
tolerance std	eng	2014/03/27	product family	-	ecn no	ELX-DG-17300-1	rel level	Released
TOLERANCES UNLESS OTHERWISE SPECIFIED	chr	-	product family	-	rel level	Released	rev	B
surface	linear	0.X ±0.30	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 2 of 5	
ISO 1302	angular	0° ±2°	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 2 of 5	

RECOMMENDED PCB LAYOUT OPTION I



DETAIL S
SCALE 6:1

spec ref	dr	Nickor Zuo	2014/02/04	projection	MM	size	A3	scale	2:1
tolerance std	eng	Nickor Zuo	2014/03/27	chr	-	ecn no	ELX-DG-17300-1	rel level	Released
	appr	Collins Lu	2014/03/27	product family	-	rel level	Released		
surface	linear	0.X	±0.30	FCI	DDR4 288Pin DIMM CONNECTOR	dwg no	10129040	rev	B
		0.XX	±0.20		PTH TERMINATION (FOR CISCO)				
		0.XXX	±0.10						
ISO 1302	angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 3 of 5	

1

2

3.

4



B



D

Pro/E File - REV C - 2009-06-09

2

STATUS:Released

Printed: Apr 01, 2014

PRODUCT PART NUMBER

10129040-

ADDITIONAL REQUIREMENTS

0: RoHS COMPLIANT

HOLD DOWNS CONFIGURATIONS

0: 3 FORKLOCKS,DIM "Y"=4.00±0.25
1: 3 FORKLOCKS,DIM "Y"=2.50±0.25
2: 3 FORKLOCKS,DIM "Y"=3.78±0.25

DIM "L", TAIL LENGTH

0: 2.60±0.25
1: 3.20±0.25

HOUSING COLOR

0: NATURAL
1: BLACK
2: BLUE

EJECTOR TYPE

CODE	COLOR	DIM"X1" MAX.EJECTORS OPEN DISTANCE	DIM"X2" MAX.EJECTORS CLOSE DISTANCE	DIM"W" EJECTOR WIDTH
0	NATURAL	162.00	149.00	(6.42)
1	BLACK			
2	BLUE			

TAIL PLATING

LF: 100u" MIN. MATE TIN
TL: 100u" MIN. TIN LEAD

CONTACT AREA PLATING

CONTACTS LUBRICATION

0: WITHOUT
1: WITH

CODE	CONTACT AREA	UNDERPLATING
1	15u" MIN.GOLD	50u" MIN.NICKEL
3	30u" MIN.GOLD	
4	30u" MIN.GXT	
5	15u" MIN.GXT	90u" MIN.NICKEL
6	30u" MIN.GOLD	
7	15u" MIN.GOLD	

NOTES:

1. MATERIALS:
HOUSING: HIGH PERFORMANCE RESINS, GLASS FILBER FILLED, UL94 V-0 RATED.
EJECTOR: HIGH PERFORMANCE RESINS, GLASS FILBER FILLED, UL94 V-0 RATED.
TERMINAL: COPPER ALLOY
FORKLOCK: COPPER ALLOY
2. DATE CODE"MMDDYYL",MMDDYY IS ASSEMBLY DATE,
L IS FCI PRODUCTION LINE.
3. SPECIFICATION:
PRODUCTION SPECIFICATION: FCI GS-12-1092.
PACKAGE SPECIFICATION: FCI GS-14-2267.
APPLICATION SPECIFICATION: FCI GS-20-0353.
4. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN FCI GS-22-008.
5. THIS PRODUCT WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10
SECONDS IN WAVE SOLDERING APPLICATION.
6. INSERTION FORCE REFERENCE:106.8 NEWTONS MAX. USING 1.50MM THICKNESS
STEEL GAUGE PER JEDEC STANDARD.

dr	Nickor Zuo	2014/02/04	projection	MM	size	A3	scale	1:1	
eng	Nickor Zuo	2014/03/27			ecn no	ELX-DG-17300-1			
chr	-	-							
appr	Collins Lu	2014/03/27	product family -			rel level Released			
FCi		title	DDR4 288Pin DIMM CONNECTOR			dwg no		10129040	rev
		PTH TERMINATION (FOR CISCO)							B
www.fci.com		cat. no.	-	Product - Customer Drw			sheet 5 of 5		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

10129040-0200001LF	10129040-0010007LF	10129040-0012207LF	10129040-0201001LF	10129040-0011107LF
10129040-0202001LF	10129040-0202007LF	10129040-0200007LF	10129040-0102001LF	10129040-0011103LF
10129040-0201007LF	10129040-0101001LF	10129040-0100001LF	10129040-0201106LF	10129040-0202206LF