




REVISIONS					
REV	ECD	DESCRIPTION	DATE	BY	APPR
A1	-	INITIAL RELEASE	4JAN 20	TZ	-



NOTES:

- CONTACT BARREL RANGE: 8AWG TO 10AWG
- RECOMMENDED CRIMP TOOLS:
HAND CRIMPER: DANIELS M300BT
- MATERIALS:
HOUSING BODY: GF PA 6/6
CONTACT: COPPER ALLOY / SILVER PLATED
- ELECTRICAL DATA:
 - CURRENT (MAX): 70A
 - VOLTAGE (MAX): 250V DC
- TECHNICAL DATA:
 - TEMPERATURE RANGE: -40°C TO 125°C
 - MATING CYCLES: >500
- RoHS COMPLIANT
- UL 94 V-0 FLAME RATING



COMPONENTS CAN BE PURCHASED SERARATELY

1	SC000531-8	4MM PIN, 8AWG CRIMPED	3
1	SC000530	4MM PIN, THREADED	2
1	PL-000727	PANEL SIDE, PLASTIC	1
QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST					
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036
1) All dimensions are in metric(mm).		DRAWN:	TZ	1JAN20	
2) Tolerances are as follows:		CHECKED:			
1 PL DEC ± 0.30		ENGINEER:			
2 PL DEC ± 0.15		APPROVAL:			
3 PL DEC ± 0.08					
3) Note reference = 					
MATERIAL SPECIFICATIONS:		CUSTOMER:			KIT, 2 POSN, MALE RECPT, PINPRM SERIES™ MACH CONT, MATES WITH PRM0400-GX-PLG
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
NEXT ASS'Y:					
		SIZE	TYPE	DWG NO:	REVISION
		B	C-	PRM0400-G3-PNL	A1
		SCALE: NONE			SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PRM0400-G3-PNL](#)