

△ N=Number of Poles
 Dim.P=(N-1)×5.08
 Dim.L=N×5.08+1.6

Poles Dim.	1P-3P	4P-9P	10P-15P	16P-21P	22P-24P
Dim.L	±0.10	±0.15	±0.25	±0.35	±0.40
Dim.P	±0.10	±0.15	±0.20	±0.30	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	11/10'12	update the drawing	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal cover: Thermoplastic (UL94V-0)
- △ ● Item ③ Terminal lever: Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item ④ Contact pin : Brass. Tin Plated.
- Item ⑤ Spring clamp : Stainless steel

Electrical:

- Voltage rating: 300 V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-28
- Stranded wire(AWG): 14-28
- Wire strip length: 11-12 mm
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C ±5°C/5 Sec
- APPROVAL:
- Critical dimension: ▽

H9 xx 5 0 x 0 xxxx G

No. OF POLES
 01: 1 POLES
 02: 2 POLES
 ;
 24: 24 POLES

RoHS compliant
 (lead<4%) △
 In copper Alloy

0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by
 customer request.
 please contact sales
 department.


Body Color
 0: BLACK
 3: Orange (RAL 2011/P)
 5: GREEN (RAL 6018/T)
 8: GREY (RAL 7004/P)

△ C: Multiple colors

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H9 5.08mm Series						
PART NO.	H9xx50x0xxxxG			DWG NO.	8H90001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Da cheng 2011.11.10	Da cheng 2011.11.10		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV: C	X.XX ±0.10	
						X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>H90150500000G</u>	<u>H90250500000G</u>	<u>H90350500000G</u>	<u>H90450500000G</u>	<u>H90550500000G</u>	<u>H90650500000G</u>
<u>H90750500000G</u>	<u>H90850500000G</u>	<u>H90950500000G</u>	<u>H91050500000G</u>	<u>H91150500000G</u>	<u>H91250500000G</u>
<u>H91350500000G</u>	<u>H91450500000G</u>	<u>H91550500000G</u>	<u>H91650500000G</u>	<u>H91750500000G</u>	<u>H91850500000G</u>
<u>H91950500000G</u>	<u>H92050500000G</u>	<u>H92150500000G</u>	<u>H92250500000G</u>	<u>H92350500000G</u>	<u>H92450500000G</u>