










SCALE 3:1
3D VIEW




PRELIMINARY


spec ref		dr		Jes Wu	2015/01/16	projection 	MM 	size	A2	scale	5:1				
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng		Jes Wu	2015/03/25			ecn no	-	rel level	Preliminary				
		chr		-	-										
		appr		-	-										
surface ISO 1302 		linear	0.X	±0.50		title	MINITEK POWER HYBRID 4.2MM HEADER ASSEMBLY	dwg no	10129817	rev	1				
	0.XX	±0.25	www.fci.com	cat. no.								-	Product-	Customer Drw	sheet 1 of 3
	0.XXX	±0.10													
	angular	0°	±3°												




2POS4P(6P)




2POS2P(4P)




2POS0P(2P)




4POS4P(8P)




4POS6P(10P)



6POS6P(12P)




8POS8P(16P)



6POS8P(14P)


POWER PIN LAYOUT (WITH OR WITHOUT SIGNAL PINS)




RECOMMENDED HOLE LAYOUT FOR 1.78MAX. THICKNESS PCB
(VIEW FROM COMPONENT SIDE)

TOTAL NUMBER OF POWER CONTACTS AND NUMBER OF SIGNAL CONTACTS	Dim"A"
2P2S2P	13.0
2P4S2P	15.0
2P6S2P	17.0
2P8S2P	19.0
2P10S2P	21.0
2P12S2P	23.0
4P2S4P	21.4
4P4S4P	23.4
4P6S4P	25.4
4P8S4P	27.4
4P10S4P	29.4
4P12S4P	31.4
6P2S6P	29.8
6P4S6P	31.8
6P6S6P	33.8
6P8S6P	35.8
6P10S6P	37.8
6P12S6P	39.8
8P2S8P	38.2
8P4S8P	40.2
8P6S8P	42.2
8P8S8P	44.2
8P10S8P	46.2
8P12S8P	48.2
2POS0P(2P)	5.0
2POS2P(4P)	9.6
2POS4P(6P)	13.8
4POS4P(8P)	18.0
4POS6P(10P)	22.2
6POS6P(12P)	26.4
6POS8P(14P)	30.6
8POS8P(16P)	34.8

spec ref	dr	Jes Wu	2015/02/16	projection	MM	size	A2	scale	5:1
tolerance std	eng	Jes Wu	2015/03/25	chr	-	ecn no	-	rel level	Preliminary
ISO 406	chr	-	-	product family	-	cat. no.	-	Product - Customer Drw	sheet 2 of 3
ISO 1101	appr	-	-	FCI	MINITEK POWER HYBRID4.2MM	10129817	1		
surface	linear	0.X	±0.50	angular	0°	±3°			
ISO 1302	angular	0°	±3°						



- 5 NOTES:
- 1. MATERIALS:
HOUSING: HIGH PERFORMANCE RESIN, UL94V-0, COLOR:NATURE
PWR CONTACT:COPPER ALLOY.
SIGNAL CONTACT:COPPER ALLOY.
 - 2. PLATING:
PWR CONTACT: 1-GOLD FLASH, 2-TIN.
SIGNAL CONTACT: GOLD FLASH OVER PALLADIUM-NICKEL PLATING.
 - 3. PRODUCT SPECIFICATION: GS-12-1288.
 - 4. APPLICATION SPECIFICATION: GS-20-0438.
 - 5. PACKAGING SPECIFICATION: GS-14-2450.



spec ref			dr		Jes Wu	2015/02/16		projection		MM		size		A2	scale		5:1					
tolerance std			eng		Jes Wu	2015/03/25						ecn no		-								
ISO 406			chr		-		-		product family		-		rel level		Preliminary							
ISO 1101			appr		-		-															
surface ✓			linear		0.X		±0.50				title		MINITEK POWER HYBRID4.2MM		dwg no		10129817		rev		1	
					0.XX		±0.25															
					0.XXX		±0.10															
ISO 1302			angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw				sheet 3 of 3			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10129817-868100LF](#) [10129817-848100LF](#) [10129817-808100LF](#) [10129817-888100LF](#) [10129817-444100LF](#)
[10129817-666100LF](#) [10129817-646100LF](#) [10129817-8A8100LF](#) [10129817-8B8100LF](#) [10129817-242100LF](#)