


USB 2.0 TYPE A PLUG



LED STATUS

FUNCTION	LEFT LED	RIGHT LED	COMMENT
Off	Off	Off	No Power
Device is booting	Solid GREEN	Solid RED	
Slave with sync	Blinking GREEN	Solid GREEN	Normal Operation
Clock Master	Blinking GREEN	Blinking GREEN	Normal Operation
Any runtime error	Blinking GREEN	Blinking RED	Normal Operation
Identify	Alternating RED and GREEN	Alternating RED and GREEN	Blinking for 6 seconds (cycle every 0.5 seconds)
Failsafe (bootloader)	Blinking RED	Blinking RED	Failsafe, Corrupt Capability (red in DC)
Upgrade	Blinking ORANGE	Blinking ORANGE	Device is upgrading

SPECIFICATIONS		
ELECTRICAL	Power Consumption	< 2 Watt
	Power Over Ethernet or USB	Class 1 IEEE 802.3af POE PD Compliant
DANTE® AUDIO	Sample Rate	48 kHz
	Bit Depth	24 bits
	Network Speed	100 Mbps
	Network Interface	Latency from 1ms
	Network Transport	Dante Audio over IP, AES67 RTP
CLIMATIC	Protection Class	IP40
	Operating Temperature	-5°C to +60°C (23°F to +140°F)
MECHANICAL	Insertion and Withdrawal Force	≥10N - ≤35N
	Weight	110g (0.243lb)
MATERIALS	Housing	Overmolded PVC 60P Black

RJD32U1-0050

**SERIES PREFIX
ADAPTER TYPE**

**USB I/O, 2 CHANNELS IN - 2 CHANNELS OUT
LENGTH IN cm
(STANDARD LENGTH = 50cm)**



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER				Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR	ANGULAR	MATERIAL:		DRN:	B.V.	DATE:	4/07/2018
X ± .05	X° ± .1	SEE PARTS LIST		OKD:	P.M.	DATE:	5/07/2018
X.X ± .01	X°X' ± .30'	DO NOT SCALE		APP'D:	P.M.	DATE:	5/07/2018
X.XX ± .005	X°XX' ± .15'	FINISH: N/A		SCALE:	NTS	SIZE:	A3
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		THIRD ANGLE PROJECTION		TITLE: AMPHE-DANTE ADAPTER, USB I/O, 2x2			
DIMENSIONS IN MILLIMETRES		PART No: 55011327-000		REV 1		SHEET 2/2	
		DRAWING No. 55011327-000-1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJD32U1-0050](#)