


LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	Flash Au Plating	0.76μ Au Plating
09	30.81	24.99	16.96	16.21	10.96	D09S33E4G*09LF	D09S33E6G*09LF
15	39.14	33.32	25.18	24.54	19.18	D15S33E4G*09LF	D15S33E6G*09LF
25	53.03	47.04	39.12	38.25	33.12	D25S33E4G*09LF	D25S33E6G*09LF

Part Number & Date Code Printing

L --> ØT=M3
X --> ØT=UNC 4-40

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)





Technical characteristics:

Insulators: self-extinguishing thermoplastic, UL class 94V0, IR or reflow process compatible

Climatic characteristics:

Operating temperature range: -55°C +225°C

FOR ALL OTHER DETAILS REFER DWG.NO: C01-8646-0000

mat'l. code				surface		tolerance		projection	product family			
-				ISO 1302 ✓		ISO 406 ISO 1101			D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title		
E	ELX-I-21461	AB	2015-07-22	angles	linear	.0±.0.1						
						.00±0.1						
						.000±0.1						
				0°±2°				MM	DD RA SOCKET CONNECTOR HIGH TEMPERATURE INSULATOR			
						scale 2:1						
				dr	JOHN SLEEBA	1996-06-21			dwg no		sheet 1 of 1	size
				engr	ALIAS BABU	2015-07-22			C01-8646-0449		A3	
				chr	MITHUN PAUL	2015-07-22						
				appd	BIJU K PAUL	2015-07-22						
sheet index	revision	E	1									
	sheet											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[D25S33E6GX09LF](#) [D09S33E6GX09LF](#)