



See note 1



PC card drilling dimensions
(after plating – thickness: 1.60 mm)



Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

Part number D50P24A*P*00LF

X--> ØT = UNC 4-40
L--> ØT = M3

GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0000

Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0±0.15 mm.

mat'l. code				surface			tolerance			projection		product family		
-				ISO 1302			ISO 406 ISO 1101			MM		D-SUB		
Ltr	ecn no	dr	date	tolerances unless otherwise specified			tolerances unless otherwise specified			MM		title		
A	-	MPE	1997/10/29	angles	linear		0.X±0.1			scale 2:1		MALE DELTA-D 50 EUROPE		
B	LS07-0281	MPE	2007/11/06	linear			0.XX±0.1					STRAIGHT SOLDER WITH NUT		
C	ELX-I-15331	AB	2013/07/24	0.XX±2'			0.XXX±0.1							
D	ELX-I-21256	AB	2015/07/14	dr	PEESSON		1997/10/27					dwg no		
-	-	-	-	enrg	ALIAS.BABU		2013/07/24					sheet 1 of 1		
-	-	-	-	chr	MITHUN.PAUL		2013/07/24					size 5		
-	-	-	-	appd	BIJU.K.PAUL		2013/07/24					A3		
sheet index				revision	D							type		
sheet				sheet	1							CUSTOMER Drawing		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[D50P24A4PX00LF](#) [D50P24A4PL00LF](#)