




REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	APR13/06	L.CHAN



RECOMMENDED P.C.B. LAYOUT  
(COMPONENT SIDE OF BOARD)

LOCATE HOLES  
Ø .005 [0.13]  
POSITION DIMENSIONS  
ARE BASIC

MATERIALS:

HOUSING: ENGINEERING THERMOPLASTIC RATING UL94V-0  
COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: MATING AREA: SELECTIVELY PLATED GOLD-PER  
PART NUMBER OPTIONS  
50 MICROINCHS [1.27 MICRONS] MIN. NICKEL OVERALL  
100 MICROINCHS [2.54 MICRONS] MIN. MATTE-TIN OVER TAIL

RECOMMENDED SOLDERING TEMPERATURE:  
WAVE SOLDERING AT 240°C MAXIMUM FOR 5 SEC MAXIMUM.

PART NUMBER: RJE05-1AA-0X10

- 1- 6µ" (0.15 MICRONS) GOLD
- 2- 15µ" (0.38 MICRONS) GOLD
- 3- 30µ" (0.78 MICRONS) GOLD
- 4- 50µ" (1.27 MICRONS) GOLD

DRAWN PAULW	DATE APR13/06	Amphenol Canada Corp.				
DESIGNED		TITLE SINGLE PORT MODULAR JACK, 10 POSITIONS, 10 CONTACTS — RoHS COMPLIANT				
CHECKED CHIGOW	APR13/06					
I. E. APPRD.						
Q. A. APPRD.						
DWG. APPRD.						
ENG. REL. NO.		DWG	DRAWING NO.  P—RJE05—1AA—0X10			REV.  A
REF. EAR # A060406						
DIMENSIONS ARE IN INCHES [mm]		CODE ID. NO.		SCALE		
03554		WT. ————		SURF. ————		SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION  
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING  
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[RJE05-1AA-0110](#) [RJE05-1AA-0110H](#) [RJE05-1AA-0210](#) [RJE05-1AA-0210H](#) [RJE05-1AA-0310](#) [RJE05-1AA-0310H](#)  
[RJE05-1AA-0410](#) [RJE05-1AA-0410H](#) [RJE05-1AA-1110](#) [RJE05-1AA-1110H](#) [RJE05-1AA-1210H](#) [RJE05-1AA-1310H](#)  
[RJE05-1AA-1410](#) [RJE05-1AA-1410H](#) [RJE05-1AA-1210](#)