




PART No.		
METAL FRONT SHELL FINISH	LED COLOR	
NICKEL	LEFT	RIGHT
RJX8FB6HRGB	RED	GREEN
RJX8FB6HRYB	RED	YELLOW
RJX8FB6HRRB	RED	RED
RJX8FB6HGRB	GREEN	RED
RJX8FB6HGYB	GREEN	YELLOW
RJX8FB6HGGB	GREEN	GREEN
RJX8FB6HYRB	YELLOW	RED
RJX8FB6HYBY	YELLOW	YELLOW
RJX8FB6HYGB	YELLOW	GREEN
RJX8FB6HUUB	BLUE	BLUE

LEFT LED
(REFER TO TABLE OF
PART No FOR
COLOR OPTIONS)

RIGHT LED

- SPECIFICATIONS:**
- 1. MATERIALS:**
- PLASTIC INSERT & HOUSING: HIGH TEMPERATURE THERMOPLASTIC FLAMMABILITY RATING UL94V-0 DSM Stanyl, 30% BLACK
 - FRONT METAL SHELL: ZINC ALLOY ZAMAK 3, NICKEL PLATE (B TYPE) .
 - CONTACTS: PHOSPHORE BRONZE, 1.27 um GOLD PLATE ON MATING SURFACES, 1.27 um NICKEL MIN UNDERPLATE. 3.81 um MIN MATTE TIN ON CONTACT TAILS.
 - LATCH LOCK AND SPRING: SPRING STEEL, NICKEL PLATE.
 - EMI/RFI HOOD: BRASS, TIN PLATE
- 2. ELECTRICAL CHARACTERISTICS:**
- RATED VOLTAGE: 125 VAC
 - TYPICAL CONTACT RESISTANCE: 20 mOhm
 - INSULATION RESISTANCE: >500 MOhm
 - DIELECTRIC STRENGTH: 1000 VAC, 60 SECONDS
 - TRANSMISSION SPECIFICATION/CLASS: COMPLIES WITH CAT6 PER TIA/EIA-568B
 - PoE+ COMPLIES WITH 802.3at Type 2



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. . NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER.				Amphenol Amphenol Australia Pty.Ltd, 22 Industry Blvd, Carrum Downs VIC 3201		
LINEAR	ANGULAR							
X ± 0.5	X' ± 1	MATERIAL: REFER SPECIFICATION				TITLE: XLRnet CONNECTOR RJ45 RECP CAT6 NON-EMI SHIELD	PART No: REFER TO TABLE OF PART No.	REV 2
X.X ± 0.1	X.X' ± 30'							
X.X ± 0.05	X.X'X" ± 15'							
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS								
DO NOT SCALE		FINISH:		DRN: T.N	DATE: 20/05/12			
				CKD: P.M	DATE: 21/05/12			
				APP'D: P.M	DATE: 21/05/12			
DIMENSIONS IN MILLIMETRES			THIRD ANGLE PROJECTION	SCALE: 3:2	SIZE: A3		DRAWING No. 55010837-000	SHEET 7/7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJX8FB6HGRB](#) [RJX8FB6HGYB](#) [RJX8FB6HRGB](#) [RJX8FB6HRRB](#) [RJX8FB6HRYB](#) [RJX8FB6HUUB](#)