



Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	25.40	38.10	50.80	63.50	76.20	88.90	101.60	114.30	127.0	139.70	152.40
Dim B	12.70	25.40	38.10	50.80	63.50	76.20	88.90	101.60	114.30	127.0	139.70
TOL	±0.15				±0.20				±0.30		

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
- Item 2 Clamp : Steel stamping , Zinc plated
- Item 3 Wire guard solder pin : Copper,Tin plated
- Item 4 Terminal screw: Steel , Zinc plating"- "slot type

- Electrical cULus IEC
- Voltage rating : 300V 1000V
 - Current rating : 65A 76A
 - Wire range : 16.00mm
 - Solid wire (AWG) : 6-20
 - Stranded wire (AWG) : 6-20
 - Torque (LB-In.) : 19LB-In
 - Screw : M4.5
 - Wire strip length : 10-11mm
 - Withstanding voltage : 2.2KV 6KV
 - Operating temperature : -40°C+115°C
 - Soldering temperature : 250°C+10°C/5 Sec
 - Safety Approval : cULus

VP xx 85 x 8 xxxx G

- 02 2 CONTACTS 0: Black
03 3 CONTACTS 5: Green (RAL 6018/T)
... 6: Blue
12 12 CONTACTS 8: Grey (RAL 7035/D)

0000 Standard @ Logo RoHS
000A Standard ANY Logo Pb<40,000ppm
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VP 12.70 Series (0.9x1.0) Contacts Pin Pitch 4.0mm ----Double parallel tail						
PART NO.	VPxx85x8xxxxG			DWG NO.	8VP0120		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Aaron 2009.11.16	Aaron 2009.11.16		X. ±0.50		
					X.X ±0.30		
					X.XX ±0.10		
					X° ±1°		
					UNIT: mm		
					SCALE: NONE		
					SHEET: 01/01		
					REV: B		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VP0285880000G](#) [VP0385880000G](#) [VP0485880000G](#) [VP0585880000G](#) [VP0685880000G](#) [VP0785880000G](#)
[VP0885880000G](#) [VP0985880000G](#) [VP1085880000G](#) [VP1285880000G](#) [VP1185880000G](#)