





SIGN	DATE	DESCRIPTION	APPROVER
△	2010.02.06	Add cULus standard	Jacke
△	2010.02.06	The Wire strip length is changed	Jacke
△	2010.03.23	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item a Clamp: Steel zinc plated.
- Item b Terminal screw: Brass Zinc plating “-” slot type
- Item c Female contact: PhBz Tin plated
- Item d Terminal (Up body): Thermoplastic (UL94V-0)
- Item e Terminal (Down body): Thermoplastic (UL94V-0)
- Item f Clampage: Steel Zinc plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In
- Screw: M2.5
- △ ● Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Safety approval:

VM xx A 5 x 1 xxxx G


POLES			G: Pb<40000ppm
02: 02 pole			
... ..			
16: 16 pole			
	Color		0000: “@” Logo (Standard) (Steel screw plating Cr ³)
	0 Black (RAL9005)		
	2 Red (RAL3001/D)		
	3 Orange(RAL2011/P)		
	4 Yellow(RAL1018/A)		
	5 Green(RAL6018/T)		
	6 Blue (RAL5015/A)		
	8 Grey(RAL7035/D)		
			000A: “ANYTEK” Mark Any special item by customer request. please contact sales department.

POLE		2	3	4	5	6	7	8
A		13.00	20.50	28.00	35.50	43.00	50.50	58.00
B		7.50	15.00	22.50	30.00	37.50	45.00	52.50
Tol.	±0.10				±0.20			
POLE	9	10	11	12	13	14	15	16
A	65.50	73.00	80.50	88.00	95.50	103.00	110.50	118.00
B	60.00	67.50	75.00	82.50	90.00	97.50	105.00	112.50
Tol.	±0.30				±0.40			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VM 7.5 mm W/O Flange Series						
PART NO.	VMxxA5x1xxxxG			DWG NO.	8VM0402		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2010.03.23	Jacke 2009.10.10		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: D	X.XX ±0.10	
						X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VM02A5510000G</u>	<u>VM03A5510000G</u>	<u>VM04A5510000G</u>	<u>VM05A5510000G</u>	<u>VM06A5510000G</u>	<u>VM07A5510000G</u>
<u>VM08A5510000G</u>	<u>VM09A5510000G</u>	<u>VM10A5510000G</u>	<u>VM11A5510000G</u>	<u>VM12A5510000G</u>	<u>VM13A5510000G</u>
<u>VM14A5510000G</u>	<u>VM15A5510000G</u>	<u>VM16A5510000G</u>	<u>VM04A5010000G</u>	<u>VM02A5010000G</u>	<u>VM05A5810000G</u>
<u>VM14A5010000G</u>	<u>VM12A5810000G</u>	<u>VM02A5810000G</u>	<u>VM07A5010000G</u>	<u>VM13A5010000G</u>	<u>VM16A5010000G</u>
<u>VM15A5810000G</u>	<u>VM13A5810000G</u>	<u>VM10A5010000G</u>	<u>VM11A5810000G</u>	<u>VM07A5810000G</u>	<u>VM12A5010000G</u>
<u>VM08A5810000G</u>	<u>VM04A5810000G</u>	<u>VM08A5010000G</u>	<u>VM10A5810000G</u>	<u>VM14A5810000G</u>	<u>VM03A5010000G</u>
<u>VM11A5010000G</u>	<u>VM15A5010000G</u>	<u>VM16A5810000G</u>	<u>VM09A5810000G</u>	<u>VM06A5810000G</u>	<u>VM03A5810000G</u>
<u>VM05A5010000G</u>	<u>VM09A5010000G</u>	<u>VM06A5010000G</u>			