




71-621740/759		SHEET 1 OF 2		A
DOCUMENT NO.		REV.		
REVISIONS				
LTR	DESCRIPTION		DATE	
A	INITIAL RELEASE			

INTERFACE REQUIREMENTS			
CONTACT SIZE	SHELL SIZE	X	Y ±.040
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	16 THRU 40	.260 ^{+.052} _{-.041}	.102
12	16 THRU 40	.118 ^{+.039} _{-.056}	.102
0,4,8	16 THRU 40	.091±.039	.102

71-621740/759


SHEET 1 OF 2

REV. A



BLACK INK STAMP "AMPHENOL", GT NUMBER, (SEE COLUMN), AND DATE CODE, (9-3895), APPROX .125 HIGH, IN APPROX LOCATION SHOWN PER 9-3856-5.
EXAMPLE:
AMPHENOL GTC00CF24-11P 0952

6	SEE NOTE 10	CONTACTS	
5	I 10-0748XX-()	INSERT	4
4	I SEE COLUMN	CLAMP ASSEMBLY	
3	I 10-564867-XX3	ADAPTER	
2	I 10-101379-XX1	GASKET	
1	I SEE COLUMN	SHELL, RECEPTACLE	
POS	QTY	PART NUMBER	DESCRIPTION
NOTE			

APPROVALS		DATE	PARTS LIST	
PREPARED BY A.Prescott		31-Oct-09	AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838	
ENGINEER IN CHARGE R.Barnes				
DESIGN MANAGER R.Barnes				
DESIGN ACTIVITY GROUP C & I			CONNECTOR, ELECTRICAL RECEPTACLE, TYPE GTC00CF(-), OLIVE DRAB CADMIUM PLATED	
THIRD ANGLE PROJECTION				
				
SIZE C	CAGE CODE 77820	DOCUMENT NO. 71-621740/759	REV. A	
SCALE: 3.0 REF: 92-622860/879			SHEET 1 OF 2	

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = ±.0005 ANGLES= ±2° .XXX = ±.010 .XX = ±.03 .X = ±.1	MATERIAL SPEC. 9-1936
DIM.& TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Sds. PER 9-3800	PROCESS SPEC. SEE NOTE 5
LEGENDS: =FLAG NOTE CALL OUT REFERENCE ONLY	

N/A	PRO/ENGINEER INFORMATION
N/A	Pro/e Model Used: GTC00CF.ASSEM
NEXT ASSEMBLY	Drawing Name: 71-621740_759

SEE SHEET 2.

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.

RELEASED / Nov . 02 2009, 11:10:42 AM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[GTC00CF32-5S\(RDS\)](#) [GTC00CF-20-29SX](#) [GTC00CF14S-6S-B30](#) [GTC00CF16-10P-LC](#) [GTC00CF20-33P](#)
[GTC00CF16-10P](#) [GTC00CF-18-12S](#) [GTC00CF20-17P](#) [GTC00CF-16S-1P](#) [GTC00CF28-59S\(025\)](#) [GTC00CF22-1P](#)
[GTC00CF22-1S](#) [GTC00CF32-5P-025](#) [GTC00CF10SL-3P](#) [GTC00CF28-15S](#) [GTC00CF28-17P](#) [GTC00CF28-3S](#)
[GTC00CF28-21S](#) [GTC00CF28-84S](#) [GTC00CF28-12P](#) [GTC00CF24-9S](#) [GTC00CF32-5P](#) [GTC00CF32-5S-LC](#)
[GTC00CF20-17S](#) [GTC00CF20-29P](#) [GTC00CF24-21S-LC](#) [GTC00CF24-22P](#) [GTC00CF24-22S](#) [GTC00CF24-67P](#)
[GTC00CF14S-2S](#) [GTC00CF14S-7S](#) [GTC00CF20-11S](#) [GTC00CF20-15P](#) [GTC00CF20-15S](#) [GTC00CF20-3P](#)
[GTC00CF20-3S](#) [GTC00CF28-3P](#) [GTC00CF-20-29S](#) [GTC00CF-18-10P](#) [GTC00CF22-22P](#) [GTC00CF22-22S-B30](#)
[GTC00CF28-51P](#) [GTC00CF28-84P](#) [GTC00CF22-22S](#)