



CONTACT SIZE	SHELL SIZE	X	Y ±.040
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	14, 16, THRU 40	.260±.052	.102
12	14, 16, THRU 40	.118±.039	.102
4,8,0	14, 16, THRU 40	.091±.039	.102

REVISIONS			
ZONE	LTR	DESCRIPTION	DATE
	B	REDRAWN SEE RECORD DWG ECN:	9-23-92 SNYDER
	C	(CLII) SEE ECN 27941	1-28-93 SNYDER
	D	(CLII) WAS "O" NOTE 13,750 WELL DEPTH ECN:28347	12-21-93 SNYDER



10	1	10-581820-XX3	NUT	3,13
9	1	10-581819-XX1	SLEEVE	13
8	1	SEE COLUMN	GROMMET	12,13
7	SEE NOTE 10		CONTACT	
6	1	10-748XX-XXX	INSERT	
5	1	10-607XX-XX	GROMMET	
4	1	10-564869-XX	SLEEVE	
3	1	10-564868-XX3	NUT	3
2	1	10-101379-XX1	GASKET	9
1	1	SEE COLUMN	SHELL	

SEE SHEET 2
NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.

COMPANY ID: 2
CODED/MS/CUST: Y
INTERNAL: N
LOTNO: N
DATE CODE: 9-3895
SEE PRINT: N

N/A
N/A
NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED
LINEAR DIMENSIONS ARE IN INCHES.
TOLERANCES: .XXX±.010,
.XX ±.03, .X ±.1, ANGLES ±2°.
OTHER STANDARDS PER 9-3800
AND DOD-D-1000. NOTE REF= (XX)

FIND NO.	QTY REQD.	FSCM NO.	PART NUMBER	DESCRIPTION	NOTE REF.
PARTS LIST					
SPECIFICATIONS		SIGNATURES	DATES	AMPHENOL CORPORATION BENDIX CONNECTOR OPERATIONS SIDNEY, N.Y.	
MATERIAL SPEC. N/A		PREPARED SNYDER	6/20/92	CONNECTOR, ELECTRICAL RECEPTACLE, REAR PANEL MOUNT, REVERSE BAYONET COUPLING, TYPE GTC030R V()-() SOLDERLESS	
		CHECKED	4/20/93		
		APPROVED			
		APPROVED D. MACAVOY	6-20-92		
PROCESS SPEC. SEE NOTE 5		SIZE	FSCM NO.		
		D 77820	71-581560/579		
		SCALE NONE	WT.	REF N/A	SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[GTC030RV36-5S\(RDS\)](#) [GTC030RV-20-11S](#) [GTC030RV2821SLC](#) [GTC030RV-16S-1P\(A24\)](#) [GTC030RV-18-1P\(025\)-LC](#) [GTC030RV14S12S](#) [GTC030RV-18-1P](#) [GTC030RV3222S](#) [GTC030RV20-4SW-025](#) [GTC030RV20-4S-025](#) [GTC030RV14S-7SY](#) [GTC030RV14S-7SX](#) [GTC030RV20-3P-LC](#) [GTC030RV20-3P-025](#) [GTC030RV28-7S-025-LC](#) [GTC030RV20-23P-025](#) [GTC030RV28-7P-025-LC](#) [GTC030RV16S-1S](#) [GTC030RV36-78S-B30](#) [GTC030RV22-19S](#) [GTC030RV20-27P-LC](#) [GTC030RV22-2P](#) [GTC030RV20-19P](#) [GTC030RV24-10P](#) [GTC030RV28-12S](#) [GTC030RV28-21P-025-LC](#) [GTC030RV32-25S-025-LC](#) [GTC030RV16S-1P-A24-C14](#) [GTC030RV28-12SW\(025\)\(LC\)](#) [GTC030RV28-21SX\(025\)\(LC\)](#) [GTC030RV20-3P\(025\)\(LC\)](#) [GTC030RV28-16P\(025\)\(LC\)](#) [GTC030RV1610P](#) [GTC030RV-10SL-3S](#) [GTC030RV-18-1S](#) [GTC030RV-22-14P](#) [GTC030RV-24-5S](#) [GTC030RV-28-16P](#) [GTC030RV-28-82S](#) [GTC030RV2821S](#) [GTC030RV2821P](#) [GTC030RV2812P](#) [GTC030RV20-4S-LC](#) [GTC030RV20-23P](#) [GTC030RV20-19P-025-LC](#) [GTC030RV20-19P-LC](#) [GTC030RV20-23S](#) [GTC030RV20-4P-B30](#) [GTC030RV20-29S](#) [GTC030RV14S-6S](#) [GTC030RV14S-6P](#) [GTC030RV28-21SX](#) [GTC030RV28-21SW](#) [GTC030RV14S-1S](#) [GTC030RV18-1S-025-LC](#) [GTC030RV16-11S](#) [GTC030RV16-11P](#) [GTC030RV16-10S](#) [GTC030RV14S-7S](#) [GTC030RV36-6P](#) [GTC030RV32-8S](#) [GTC030RV32-25S](#) [GTC030RV36-5S](#) [GTC030RV36-3S](#) [GTC030RV28-51S-025-LC](#) [GTC030RV18-1SX-025-LC](#) [GTC030RV28-16PW-025-LC](#) [GTC030RV28-21PW-025-LC](#) [GTC030RV28-21S-025-B30](#) [GTC030RV28-21P-025](#) [GTC030RV28-51P-025-LC](#) [GTC030RV20-11S-025-C36](#) [GTC030RV28-21PX-025-LC](#) [GTC030RV20-23S-LC-025](#) [GTC030RV28-21SW-025-LC](#) [GTC030RV28-6PW-025-LC](#) [GTC030RV20-23P-025-LC](#) [GTC030RV28-21PW-025](#) [GTC030RV28-16S-025-LC](#) [GTC030RV18-11P-025-LC](#) [GTC030RV28-16P-025-A24](#) [GTC030RV20-15S](#) [GTC030RV24-7S](#) [GTC030RV20-27S](#) [GTC030RV28-51S](#) [GTC030RV20-24S](#) [GTC030RV32-1P](#) [GTC030RV20-15P](#) [GTC030RV20-19S](#) [GTC030RV24-7P](#) [GTC030RV32-64P](#) [GTC030RV20-11P](#) [GTC030RV20-19S-RDS-025](#) [GTC030RV20-4S-025-LC](#) [GTC030RV20-4S-LC-025](#) [GTC030RV22-22P-027](#) [GTC030RV28-21S-025-LC](#) [GTC030RV28-84P](#) [GTC030RV14S-5P-A24](#) [GTC030RV16-10P-025-LC](#)