


SIGN	DATE	DESCRIPTION	APPROVER
△	01/22'13	update the drawing	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

△ Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Body(contact pin): Brass, Tin plated
- Item ④ Insulator(Cover): Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 10-24
- Wire strip length: 11-12mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 

△ Critical dimension: ▽

H2 xx 10 x 0 xxxx G

△No. OF POLES

- 01: 1 POLES
- 02: 2 POLES
- :
- 12: 12 POLES

△ COLOR


- 0: BLACK
- 2: Red (RAL3001/D)
- 5: GREEN (RAL 6018/T)
- 8: GREY (RAL 7004/P)
- C: Multiple colors





RoHS compliant
(lead<4%) △
In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H2 10.0 Series						
PART NO.	H2xx10x0xxxxG			DWG NO.	8H20002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Da cheng 2013.01.22	Da cheng 2013.01.22		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: C	X.XX ±0.10	
						X* ±1*	



△ P.C.B. LAYOUT
Top view

POLE	1	2	3	4	5	6
Dim A	12.50	20.00	30.00	40.00	50.00	60.00
Dim B		10.00	20.00	30.00	40.00	50.00
Tol.	±0.25					
POLE	7	8	9	10	11	12
Dim A	70.00	80.00	90.00	100.00	110.00	120.00
Dim B	60.00	70.00	80.00	90.00	100.00	110.00
Tol.	±0.40					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[H20210800000G](#) [H20310800000G](#) [H20410800000G](#) [H20510800000G](#) [H20610800000G](#) [H20710800000G](#)
[H20810800000G](#) [H20910800000G](#) [H21010800000G](#) [H21110800000G](#) [H21210800000G](#)