





REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASE NEW DWG FORMAT	08/22/14	DRACK	TOMMY



- NOTES: UNLESS OTHERWISE SPECIFIED
- MATERIAL: COPPER ALLOY, SILVER PLATED
 - SPECIFICATIONS:
 - 2.1 RATED CURRENT: 180 AMPS
 - 2.2 CONTACT RESISTANCE: <0.3 MILLIOHM
 - 2.3 AVAILABLE WIRE RANGE: 50 MM²
 - 2.4 RoHS COMPLIANT
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SECTION A-A



	SEE PART NUMBER				
	CHART				
QUANTITY	PART NUMBER	DESCRIPTION	ITEM		
MATERIALS LIST					
<div>UNLESS OTHERWISE SPECIFIED</div> <div>1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08</div> <div>Fractions ±1/64 Angles ±1°</div> <div>3) Note reference = </div>		SIGNATURES		DATE	
		DRAWN: Drack		08/22/14	
		CHECKED:			
		ENGINEER:			
MATERIAL SPECIFICATIONS:		APPROVAL:		<div>Amphenol</div> <div>Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036</div>	
		CUSTOMER:			
		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
PROCESS SPECIFICATIONS:		ECO-MATE,10MM RADSOK,CRIMP 50MM ²			
NEXT ASSY:		SIZE	TYPE	DWG NO:	REVISION
		B	C-	HS50DCS	B1
		SCALE:	2 : 1		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HPDHS](#)