

REVISIONS

REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASE NEW DWG FORMAT	08/22/14	DRACK	TOMMY



TITLE: ECO-MATE,10MM RADSOCK,CRIMP 95MM²

DWG NO: HS95DCS

REV: B1


SH: 1

OF: 1




NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL: COPPER ALLOY, SILVER PLATED
2. SPECIFICATIONS:
 - 2.1 RATED CURRENT: 300 AMPS
 - 2.2 CONTACT RESISTANCE: <0.3 MILLIOHM
 - 2.3 AVAILABLE WIRE RANGE: 95 MM²
 - 2.4 RoHS COMPLIANT
3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SECTION A-A



QUANTITY	PART NUMBER	SEE PART NUMBER CHART		ITEM
MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED	SIGNATURES	DATE		
1) All dimensions are in metric(mm).	DRAWN:	Drack	08/22/14	
2) Tolerances are as follows:	CHECKED:			
1 PL DEC ± 0.30	Fractions $\pm 1/64$			
2 PL DEC ± 0.15	Angles $\pm 1^\circ$			
3 PL DEC ± 0.08				
3) Note reference =	ENGINEER:			
MATERIAL SPECIFICATIONS:	APPROVAL:			
PROCESS SPECIFICATIONS:	CUSTOMER:			
THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
NEXT ASS'Y:	SCALE:	2 : 1		SHEET 1 OF 1
	SIZE	TYPE	DWG NO:	REVISION
	B	C-	HS95DCS	B1

Amphenol
Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

ECO-MATE,10MM RADSOCK,CRIMP 95MM²

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HS95DCS](#)