







SECTION P-P

N = Number of poles

Dim.A	$N \times 7.62$
Dim.B	$(N-1) \times 7.62$
Dim.C	$(N+1) \times 7.62$
Dim.D	$(N+2) \times 7.62$

Dimension

Poles	Tolerance
2P-5P	± 0.20
6P-10P	± 0.30
11P-16P	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Terminal(housing) : PA66 (UL94V-0)
- Item ② Terminal(cover) : PA66 (UL94V-0) (ET 7.62)
- Item ③ Terminal screw : Steel Zinc plating " - " slot type (ET 7.62)
- Item ④ Clamp : Brass, Ni plated (ET 7.62)
- Item ⑤ Female contact : Copper, Tin plated
- Item ⑥ With flange screw : Steel Zinc plating M3 (ET 7.62)

Electrical

- Voltage rating: 600VAC
- Current rating: 41A
- Solid wire (AWG): 8-24
- Stranded wire(AWG): 8-24
- Torque: 9.0 Lb-In
- Screw: M3.5
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension:

KT xx 0 1 x 4 xxxx G

No. OF POLES
02: 2 POLES
:
16: 16 POLES

COLOR

0 Black (RAL9005)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
C Green(RAL6018/U)

G: Pb<4000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KT 7.62 Series 2P-16P " - " Screw (Flange With Screw)						
PART NO.	KTxx01x4xxxxG			DWG NO.	8KT0004		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Aaron 2011.10.18	Aaron 2011.10.18			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: B		X.XX ±0.10
							X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[KT0201540000G](#) [KT0301540000G](#) [KT0401540000G](#) [KT0501540000G](#) [KT0601540000G](#) [KT0701540000G](#)
[KT0801540000G](#) [KT0901540000G](#) [KT1001540000G](#) [KT1101540000G](#) [KT1201540000G](#) [KT1301540000G](#)
[KT1401540000G](#) [KT1501540000G](#) [KT1601540000G](#)