




2P mark



POLES	DIM L	DIM B	TOLERANCE	POLES	DIM L	DIM B	TOLERANCE
2P	10.16	5.08	+0.15 -0.15	13P	66.04	60.96	+0.35 -0.35
3P	15.24	10.16		14P	71.12	66.04	
4P	20.32	15.24		15P	76.20	71.12	
5P	25.40	20.32		16P	81.28	76.20	
6P	30.48	25.40		17P	86.36	81.28	
7P	35.56	30.48	+0.25 -0.25	18P	91.44	86.36	+0.40 -0.40
8P	40.64	35.56		19P	96.52	91.44	
9P	45.72	40.64		20P	101.60	96.52	
10P	50.80	45.72		21P	106.68	101.60	
11P	55.88	50.80		22P	111.76	106.68	
12P	60.96	55.88		23P	116.84	111.76	
				24P	121.92	116.84	

SIGN	DATE	DESCRIPTION	APPROVER
△	02/01'07	Part No. is changed.	Aaron
△	09.4.27	Part No. wire strip ,operating temperature are changed.	JODY
△	11/25'09	The Grey code changed from RAL7004/P to RAL7035/D	Kind
△	03/13'10	Add the 2P mark	RUNNER
△	04/08'10	Get rid of the rib	RUNNER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal body:Thermoplastic (UL94V-0)
- Item 2 Terminal cover:Thermoplastic (UL94V-0)
- Item 3 Insulating spacer:Thermoplastic (UL94V-0)
- Item 4 Female contact:PhBz (CuSn) Tin plated
- Item 5 Wire guard:Stainless Steel

Electrical: cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-26
- Stranded wire(AWG): 14-26
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature:
- Safety Approval:

PART NO.

HN xx 50 x 0 xxxx G △ △

Poles

- 02 2Contacts
- 03 3Contacts
- 24 24Contacts

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)


0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

RoHS
Pb<40,000ppm

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HN 5.08 SERIES WITHOUT FLANGE				DWG NO.		8HN0001	
PART NO.		HNxx50x0xxxxG				DWG NO.		8HN0001	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
			Runner 2010.04.08	Aaron 2009.06.18			UNIT: mm	X.	±0.50
							SCALE: NONE	X.X	±0.30
					SHEET: 01/01		REV.: H	X.XX	±0.10
								X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>HN0250500000G</u>	<u>HN0350500000G</u>	<u>HN0450500000G</u>	<u>HN0550500000G</u>	<u>HN0650500000G</u>	<u>HN0750500000G</u>
<u>HN0850500000G</u>	<u>HN0950500000G</u>	<u>HN1050500000G</u>	<u>HN1150500000G</u>	<u>HN1250500000G</u>	<u>HN1350500000G</u>
<u>HN1450500000G</u>	<u>HN1550500000G</u>	<u>HN1650500000G</u>	<u>HN1750500000G</u>	<u>HN1850500000G</u>	<u>HN1950500000G</u>
<u>HN2050500000G</u>	<u>HN2150500000G</u>	<u>HN2250500000G</u>	<u>HN2350500000G</u>	<u>HN2450500000G</u>	