


SECTION P-P



Dimension

Dim L	$(N+1) \times 10.16 + 7.6$
Dim B	$(N-1) \times 10.16$
Dim C	$(N+1) \times 10.16$
Dim D	$(N-1) \times 10.16$

N=Number of poles

POLES	TOL
2p-5p	$\pm 0.25$
6p-8p	$\pm 0.35$
9p-12p	$\pm 0.45$

SIGN	DATE	DESCRIPTION	APPROVER
△	07/13`12	The dimension is added	Chen Bo
△	03/04`14	update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item a Terminal(housing): Thermoplastic, UL 94 - V0.
- Item b Male contact pin: Copper, Gold plated
- Item c With flange nut : Steel zinc plated M3

Electrical: cULus / IEC

- Voltage rating: 300V / 1000V
- Current rating: 55A / 76A
- Withstanding Voltage: 1.6 KV / 8 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C $\pm$ 5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ▽

△ EW xx 62 x 1 xxxx G	Color	G RoHS compliant (lead<4%) In copper Alloy
Solid Block	02 2Contacts	0000 Standard @ Logo
03 3Contacts	12 12Contacts	000A Standard ANY Logo
	0 Black (RAL9005)	Any special item by customer request, please contact sales department.
	2 Red (RAL3001/D)	
	3 Orange (RAL2011/P)	
	4 Yellow (RAL1018/A)	
	5 Green (RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey (RAL7035/D)	
	9 White (RAL1102)	
	C Green (RAL6018/U)	

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EW 10.16 Series 2p-12p Right -Angle with flange ( down )						
PART NO.	EWxx62x1xxxxG			DWG NO.	8EW0004		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Chen Bo	Chen Bo		UNIT: mm	X.	$\pm 0.50$
		03/04`14	03/04`14		SCALE: NONE	X.X	$\pm 0.30$
						X.XX	$\pm 0.10$
						X°	$\pm 1°$



SHEET: 01/01

REV.: D

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[EW0562510000G](#) [EW0862510000G](#) [EW0662510000G](#) [EW0762510000G](#) [EW0362510000G](#) [EW0462510000G](#)  
[EW0262510000G](#) [EW0962510000G](#) [EW1062510000G](#) [EW1162510000G](#) [EW1262510000G](#)