





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-8B0713	2008/11/24	TOMMY	CHANGE THE NOTE
D	LEN-930473	2009/03/04	ZhaoRongFu	Add Waterproof Rate
E	LEN1810176	2018/01/16	Mark	CHANGE THE NOTE



Recommended Panel Cut-Out



- Notes:
- * (Ø) Important Dimension To Check
 - * Waterproof Rate: IP67
 - * LED Spec.
 - Ø5mm, Green
 - Lens Color: Water Clear
 - Viewing Angle: 15°
 - Absolute Maximum Rating (@25°C);
 - * Power Dissipation: 76mW
 - * Forward Current (IF): 30mA
 - * Reverse Voltage (VR): 5V
 - Forward Voltage (VF): typ. 3.3V (@IF=20mA, 25°C)
 - Luminous Intensity (IV): typ. 22000mcd (@IF=20mA, 25°C)
 - * Internal Current Limiting Resistor: 47Ω
 - * Recommended Operating Voltage: DC 4V
 - * LED Holder: Copper Alloy, Nickel Plating
 - * O-Ring: EPDM, Black
 - * Screw Nut: Copper Alloy, Nickel Plating
 - * Operating Temperature: -40~+80°C
 - * Panel Thickness: 6.5mm max.



UNIT:mm



TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE

Waterproof Led (Ø5mm)
Green, Solder Type

SCALE

2:1

SIZE

A4

SHEET

1

OF

1

REV.

E

WC-REV.

A.2

(Ø): Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

L08-01GBAS-MR7001

DWG NO

L08-01GBAS-MR7001

CUSTOMER

ALTW

DRAWN BY

Mark

CHECKED BY

Neo

APPROVED BY

Max

DATE

2018/01/16

DATE

2018/01/16

DATE

2018/01/16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[L08-01GBAS-MR7001](#)