







Conn.
Pin Assignments
Front View




Recommended
Panel Cut-Out



Note:

- * **① Important Dimension.**
- * Waterproof Rate: IP67.
- * Connector: Nylon, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Shield: Copper Alloy, Nickel Plated.
- * O-Ring: Silicone, UL94V-0, Gray.
- * Recommended Gauge: 12 Awg
- *  Use without waterproof cap or dust cap
- Panel Thickness Max: 6.0mm
- Panel Thickness Min: 2.0mm

UNIT: mm			TITLE M23 Panel ASS'Y Type, M CON, M PIN			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO LJ23-06PMMC-SF7001		DRAWN BY Ethan		DATE 2018-01-15				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±			SCALE 1:1		SIZE A4			SHEET 1 OF 2		DWG NO LJ23-06PMMC-SF7001		CHECKED BY Feng Li		DATE 2018-01-15		
			REV. C		WC-REV. A.4			QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2018-01-15		



最後將 A 包裝與 B 包裝及(10)組裝說明書一同裝入(9) 6 號由任袋中，即放入紙箱

UNIT:mm				TITLE M23 Panel ASS'Y Type, M CON, M PIN			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO LJ23-06PMMC-SF7001		DRAWN BY Ethan		DATE 2018-01-15		
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1		SCALE 1:1		SIZE A4		SHEET 2 OF 2			DWG NO LJ23-06PMMC-SF7001		CHECKED BY Feng Li		DATE 2018-01-15		
		REV. C		MC-REV. A.4		(QC): Inspection item			CUSTOMER ALTW		APPROVED BY Jerry		DATE 2018-01-15		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LJ23-06PMMC-SF7001](#)