



## FEATURES

- Excellent RF Shielding, better than 90 dB
- UV and weather resistant
- Flexible and easy to use

## LMR<sup>®</sup>-400 FLEXIBLE LOW LOSS CABLE ASSEMBLIES

Times LMR cable assemblies are high performance broadband, flexible, low-loss RF coaxial cables that can be used virtually anywhere, either indoors or outdoors. As a completely Times manufactured solution, performance and reliability are assured.

## Mechanical Properties


	Units	
Diameter	in (mm)	0.405 (10.287)
Weight	lb/ft (kg/m )	0.068 (0.10)
Minimum Bend Radius	in(mm)	1.00 (25.4)
Operating Temperature	°F (°C)	-40° to 185°(-40 to 85)
Tensile Strength	lb (kg)	160 (72.6)
Bending Moment	ft lb (N-m)	0.5 (0.68)
Flat Plate Crush	lb/in (kg/mm)	40 (0.71)
Storage Temp	°F (°C)	-94 to 185 (-70 to 85)

## Electrical Properties

	Units	
Impedance	Ω	50 +/- 2
Maximum Frequency	GHz	8.0
Capacitance	pF/ft (pF/m)	23.9 (78.4 )
Velocity of Propagation		84%
Delay	ns/ft (ns/m)	1.20 (3.94)
Shielding		>90dB minimum
Voltage Withstand	Volts DC	2500
Jacket Spark	Volts RMS	8000
Attenuation	dB/ft	dB/m
900 MHz	0.04	(0.13)
2.5 GHz	0.07	(0.23)
5.8 GHz	0.11	(0.36)

## KEY APPLICATIONS

- Antenna feeder runs
- Inter/intra cabinet jumpers
- Internal component equipment wiring
- GPS system wiring




# LMR<sup>®</sup>-400

FLEXIBLE LOW LOSS CABLE ASSEMBLIES

## Ordering Guide

# LMR400- NMNM-3.0 F



Heritage—in the air and on the ground, thousands of assemblies built over decades



Global manufacturing capability: US, Mexico, India & China



Assembled and tested LMR assemblies provide assured performance

### WORLD HEADQUARTERS

358 Hall Avenue, Wallingford, CT 06492  
1-800-867-2629

**TT** **TIMES**  
MICROWAVE SYSTEMS  
AN AMPHENOL COMPANY

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LMR400NMNM6.0F](#)