


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASE NEW DWG FORMAT	Jul.15,2014	Tod	Tommy
B2	-	UPDATE THE DURABILITY	Jun.27,2015	Drack	Tommy
B3	-	UPDATED	08DEC15	MRF	Tommy

		Cable OD Range
1	MA3TNxxx00-S1	4.5~7.5 mm
2	MA3TNxxx00-S2	7.5~11.0 mm
3	MA3TNxxx00-S3	11.0~15.0 mm


-	MA3TNP1900-S3	M23, RECP, BULKHEAD, 19POS, P TYPE	27
-	MA3TNP1900-S2	M23, RECP, BULKHEAD, 19POS, P TYPE	26
-	MA3TNP1900-S1	M23, RECP, BULKHEAD, 19POS, P TYPE	25
-	MA3TNE1900-S3	M23, RECP, BULKHEAD, 19POS, E TYPE	24
-	MA3TNE1900-S2	M23, RECP, BULKHEAD, 19POS, E TYPE	23
-	MA3TNE1900-S1	M23, RECP, BULKHEAD, 19POS, E TYPE	22
			21
-	MA3TNP1700-S3	M23, RECP, BULKHEAD, 17POS, P TYPE	20
-	MA3TNP1700-S2	M23, RECP, BULKHEAD, 17POS, P TYPE	19
-	MA3TNP1700-S1	M23, RECP, BULKHEAD, 17POS, P TYPE	18
-	MA3TNE1700-S3	M23, RECP, BULKHEAD, 17POS, E TYPE	17
-	MA3TNE1700-S2	M23, RECP, BULKHEAD, 17POS, E TYPE	16
-	MA3TNE1700-S1	M23, RECP, BULKHEAD, 17POS, E TYPE	15
			14
-	MA3TNP1600-S3	M23, RECP, BULKHEAD, 16POS, P TYPE	13
-	MA3TNP1600-S2	M23, RECP, BULKHEAD, 16POS, P TYPE	12
-	MA3TNP1600-S1	M23, RECP, BULKHEAD, 16POS, P TYPE	11
-	MA3TNE1600-S3	M23, RECP, BULKHEAD, 16POS, E TYPE	10
-	MA3TNE1600-S2	M23, RECP, BULKHEAD, 16POS, E TYPE	9
-	MA3TNE1600-S1	M23, RECP, BULKHEAD, 16POS, E TYPE	8
			7
-	MA3TNP1200-S3	M23, RECP, BULKHEAD, 12POS, P TYPE	6
-	MA3TNP1200-S2	M23, RECP, BULKHEAD, 12POS, P TYPE	5
-	MA3TNP1200-S1	M23, RECP, BULKHEAD, 12POS, P TYPE	4
-	MA3TNE1200-S3	M23, RECP, BULKHEAD, 12POS, E TYPE	3
-	MA3TNE1200-S2	M23, RECP, BULKHEAD, 12POS, E TYPE	2
-	MA3TNE1200-S1	M23, RECP, BULKHEAD, 12POS, E TYPE	1
QUANTITY	PART NUMBER	DESCRIPTION	ITEM

DRAWING TITLE									
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE		Amphenol			
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64 2 PL DEC ±0.15 Angles ±1° 3 PL DEC ±0.08		DRAWN: Drack		Jun.27,2015		Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036			
MATERIAL SPECIFICATIONS:		CHECKED:				M23, RECP, BULKHEAD, THREADED			
		ENGINEER:							
		APPROVAL:							
PROCESS SPECIFICATIONS:		CUSTOMER:				SIZE TYPE DWG NO: REVISION			
		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.							
NEXT ASSY:		SCALE:		NONE		C-MA3TNxxx00-Sx		SHEET 1 OF 1	



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:
INSULATION INSERT: PA66,UL94 V0
SEAL: VITON
HOUSING BODY: ZINC DIE CAST, NICKEL PLATED
2. SPECIFICATIONS:
 - 2.1 CURRENT RATING: 10 AMPS - 12 POSITION
 9 AMPS - 16 POSITION
 9 AMPS - 17 POSITION
 7 AMPS - 19 POSITION
 - 2.2 VOLTAGE RATING: 160V AC/DC - 12 POSITION
 125V AC/DC - 16 POSITION
 125V AC/DC - 17 POSITION
 63V AC/DC - 19 POSITION
 - 2.3 OPERATING TEMPERATURE: -20°C TO +130°C
 - 2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2
MILLIAMPS CURRENT LEAKAGE @ 2500 VOLTS AC.
 - 2.5 DEGREE OF PROTECTION: IP67 (MATED CONDITION)
 - 2.6 DEGREE OF POLLUTION: 3 PER UL840
 - 2.7 OVERVOLTAGE CATEGORY: III PER UL840
 - 2.8 MATING CYCLE DURABILITY: >500 CYCLES
 - 2.9 RoHS COMPLIANT
3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MA3TNP1200-S1](#)