





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



RECOMMENDED PCB LAYOUT



N = Number of poles
Dim A=Nx5.08+2
Dim B=(N-1)x5.08

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ⑥ Terminal(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V/300V/300V
- Current rating: 20A/20A/20A
- Withstanding Voltage: 1.6 KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:



OQ xx 5 4 x 0 x3xx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<4000ppm
0300: "@" Logo (Standard)
030A: "ANYTEK" Mark
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OQ 5.08mm Vertical /Close Series 2p-24p(with latch holder)								
PART NO.	OQxx54x0x3xxG			DWG NO.	80Q07073				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Jacke 2010.03.22	Jacke 2009.10.22					UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30			
					SHEET: 01/01	REV.: B	X.XX ±0.10		
								X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>OQ0254500300G</u>	<u>OQ0354500300G</u>	<u>OQ0454500300G</u>	<u>OQ0554500300G</u>	<u>OQ0654500300G</u>	<u>OQ0754500300G</u>
<u>OQ0854500300G</u>	<u>OQ0954500300G</u>	<u>OQ1054500300G</u>	<u>OQ1154500300G</u>	<u>OQ1254500300G</u>	<u>OQ1354500300G</u>
<u>OQ1454500300G</u>	<u>OQ1554500300G</u>	<u>OQ1654500300G</u>	<u>OQ1754500300G</u>	<u>OQ1854500300G</u>	<u>OQ1954500300G</u>
<u>OQ2054500300G</u>	<u>OQ2154500300G</u>	<u>OQ2254500300G</u>	<u>OQ2354500300G</u>	<u>OQ2454500300G</u>	<u>OQ0454000300G</u>
<u>OQ0254000300G</u>	<u>OQ0354800300G</u>	<u>OQ0454800300G</u>	<u>OQ1754800300G</u>	<u>OQ1954000300G</u>	<u>OQ0354000300G</u>
<u>OQ0254800300G</u>	<u>OQ1954800300G</u>	<u>OQ2054800300G</u>	<u>OQ2154000300G</u>	<u>OQ2454800300G</u>	<u>OQ1154000300G</u>
<u>OQ1154800300G</u>	<u>OQ1454800300G</u>	<u>OQ1354000300G</u>	<u>OQ1854800300G</u>	<u>OQ1554000300G</u>	<u>OQ1754000300G</u>
<u>OQ1254000300G</u>	<u>OQ1654000300G</u>	<u>OQ1454000300G</u>	<u>OQ1354800300G</u>	<u>OQ1654800300G</u>	<u>OQ1854000300G</u>
<u>OQ2254000300G</u>	<u>OQ2054000300G</u>	<u>OQ2154800300G</u>	<u>OQ2254800300G</u>	<u>OQ2454000300G</u>	<u>OQ2354800300G</u>
<u>OQ2354000300G</u>	<u>OQ1554800300G</u>	<u>OQ0554000300G</u>	<u>OQ0654000300G</u>	<u>OQ1054000300G</u>	<u>OQ0754000300G</u>
<u>OQ0654800300G</u>	<u>OQ0854000300G</u>	<u>OQ0554800300G</u>	<u>OQ0754800300G</u>	<u>OQ0854800300G</u>	<u>OQ0954000300G</u>
<u>OQ1054800300G</u>	<u>OQ0954800300G</u>	<u>OQ1254800300G</u>			