


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JULY-1-2014	BEN	TOMMY



P/N	CONTACT PLATING(MATING AREA)	
MP14M23T	TIN PLATING OVER NICKEL.	
MP14M23S	SILVER PLATING OVER NICKEL.	
MP14M23F	GOLD FLASH PLATING OVER NICKEL.	
MP14M23G10	10 μ "GOLD PLATING OVER NICKEL.	
MP14M23G15	15 μ "GOLD PLATING OVER NICKEL.	
MP14M23G30	30 μ "GOLD PLATING OVER NICKEL.	

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:
 - 1.1. CONTACT BODY: COPPER ALLOY.
 - 1.2. POSITIONING CLIP: COPPER ALLOY.
2. SPECIFICATIONS:
 - 2.1 CURRENT RATING: 13A(MAX).
 - 2.2 TERMINATION TYPE: CRIMPING.
 - 2.3 WIRE RANGE: 16~14AWG.
3. SUITABLE SOCKET TYPE: MS14M23xx.
4. ROHS COMPLIANT.
5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED	SIGNATURES	DATE	Amphenol
1) All dimensions are in metric(mm).	DRAWN: BEN	JULY-1-2014	
2) Tolerances are as follows: 1 PL DEC ± 0.30 Fractions $\pm 1/64$ 2 PL DEC ± 0.10 Angles $\pm 1^\circ$ 3 PL DEC ± 0.08	CHECKED:		
3) Note reference = 	ENGINEER:		
MATERIAL SPECIFICATIONS:	CUSTOMER:	APPROVAL:	
PROCESS SPECIFICATIONS:	THE DRAWING IS SUPPLIED FOR REFERENCE ONLY. DRAWINGS, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF AMPHENOL CORPORATION. ALL RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		
NEXT ASSY:	None	TYPE: C-	SIZE: B
		DWG NO: MP14M23xx	REVISION: B1
		SHEET 1 OF 1	

TITLE: ECO-MATE PIN CONTACT, MACHINE, 16-14AWG, SIZE 16

DWG NO: MP14M23xx

REV: B1

SH: 1

OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MP14M23F](#)