


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JUN-18-2014	BEN	TOMMY



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:

1.1. CONTACT BODY: COPPER ALLOY.
1.2. OUTER SPRING: STAINLESS STEEL.

2. SPECIFICATIONS:

2.1 CURRENT RATING: 7.5A(MAX).
2.2 TERMINATION TYPE: CRIMPING.
2.3 WIRE RANGE: 20-22AWG.
3. SUITABLE SOCKET TYPE: MS20W23xx.
4. ROHS COMPLIANT.
5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

P/N	CONTACT PLATING(MATING AREA)
MP20W23F	GOLD FLASH PLATING OVER NICKEL.
MP20W23G10	10μ"GOLD PLATING OVER NICKEL.
MP20W23G15	15μ"GOLD PLATING OVER NICKEL.
MP20W23G30	30μ"GOLD PLATING OVER NICKEL.

ITEM	QUANTITY	PART NUMBER	DESCRIPTION	
MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED	SIGNATURES	DATE	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
1) All dimensions are in metric(mm).	DRAWN:	JUN-18-2014		
2) Tolerances are as follows:	CHECKED:			
1 PL DEC ±0.30 2 PL DEC ±0.16 3 PL DEC ±0.08	ENGINEER:			
3) Note reference = 	APPROVAL:			
MATERIAL SPECIFICATIONS:	CUSTOMER:		ECO-MATE, PIN CONTACT MACHINE, 20-22AWG, SIZE 20	
PROCESS SPECIFICATIONS:				
NEXT ASSY:			SIZE B TYPE C- DWG NO: MP20W23xx REVISION B1	
	SCALE NONE		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MP20W23F](#)