




REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	FIRST RELEASE	May/27/2017	ToD TOMMY
A2	-	Modify the current rating	Jul/10/2017	White TOMMY



NOTES : (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL :

1.1. CONTACT BODY : COPPER ALLOY.

1.2. POSITIONING CLIP : COPPER ALLOY.

2. SPECIFICATIONS :

2.1 CURRENT RATING : 35A(MAX).

2.2 TERMINATION TYPE : CRIMPING.

2.3 WIRE RANGE : 10~12 AWG.

3. SUITABLE SOCKET : MP10B23xx.

4. RoHS COMPLIANT.

5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

P/N	CONTACT PLATING(MATING AREA)
MS10B23T	TIN PLATING OVER NICKEL.
MS10B23S	SILVER PLATING OVER NICKEL.
MS10B23F	GOLD FLASH PLATING OVER NICKEL.
MS10B23G5	5 μ "GOLD PLATING OVER NICKEL.
MS10B23G10	10 μ "GOLD PLATING OVER NICKEL.
MS10B23G15	15 μ "GOLD PLATING OVER NICKEL.
MS10B23G30	30 μ "GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES	
1) All dimensions are in millimeters. 2) Tolerances are as follows: 1 Pl. DEC ±0.30 3 Pl. DEC ±0.08 3) Note reference = Δ		DRAWN:	DATE: Jul/10/2017
		ENGINEER:	
MATERIAL SPECIFICATIONS:		CUSTOMER:	
PROCESS SPECIFICATIONS:		THIS DRAWING IS STANDARD FOR INTERCOMPATIBILITY AND DESIGN FEATURES. SPECIFICATIONS AND PERFORMANCE DATA OF REPRODUCTION ARE LISTED. ALL MANUFACTURING VARIATIONS.	
NEXT ASSTY:		SIZE: B TYPE: C- SCALE: NONE	ECO-MATE SOCKET CONTACT MACHINE, FEMALE, CONTACT 2.5mm DWG NO: MS10B23xx REVISION: A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS10B23G5](#) [MS10B23T](#) [MS10B23G15](#) [MS10B23F](#) [MS10B23S](#) [MS10B23G30](#) [MS10B23G10](#)