





SJS830250P_C


SJS830250P_C

PART NO.	CONTACTS SUPPLIED	PART MARKING
SJS830250P	NONE	SJS830250P
SJS830251P	(2) M39029/57-354	

REV	ECN	APP'D
-	7480	







WHITE MARKING
TWO SIDES



RED MARKING NOT VISIBLE
IN CLOSED POSITION
TWO SIDES

NOTES:

- MATERIALS:
HOUSING: POLYETHERIMIDE
CONTACT RETAINER: STAINLESS STEEL
GROMMET & FACE SEAL: SILICONE RUBBER PER A-A-59588
EMI SPRING: BERYLLIUM COPPER
- HOUSING: NICKEL, 200 MICROINCHES MINIMUM
OVER COPPER, 120 MICROINCHES MINIMUM
EMI SPRING: NICKEL, 100 MICROINCHES MINIMUM
- PART ACCEPTS SOCKET CONTACTS PER M39029/57-354
- PART MATES WITH SJS830270P/271P
- EST. WEIGHT: 1.5 GRAMS
- SUPPLIED WITH DUST CAP.

DIMENSIONS	TOLERANCES	PROJECTION	TITLE			
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±2.0°		Amphenol Pcd SPECIFICATION DRAWING			
ORIGINAL 	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA		ENGR ANDREW.WANG Feb-28-15	SIZE B DWG NO. SJS830250P_C		
			CHKD  4/13/15	REV -		
			APPD  4/14/15	CODE: 58982	SCALE: 4:1	SHEET 1 OF 1

SJS830250P_C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SJS830250P](#)