


REVISIONS

REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JULY-1-2014	BEN	TOMMY



NOTES : (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL :
 - 1.1. CONTACT BODY : COPPER ALLOY.
 - 1.2. POSITIONING CLIP : STAINLESS STEEL.
2. SPECIFICATIONS :
 - 2.1 CURRENT RATING : 7.5A(MAX).
 - 2.2 TERMINATION TYPE : CRIMPING.
 - 2.3 CRIMP WIRE RANGE : 22~20AWG.
3. ALL DIMENSION ARE FOR REFERENCE USE ONLY.
4. ROHS COMPLIANT.

P/N	CONTACT PLATING(MATING AREA)		
MS20W23F	GOLD FLASH PLATING OVER NICKEL.		
MS20W23G10	10µ"GOLD PLATING OVER NICKEL.		
MS20W23G15	15µ"GOLD PLATING OVER NICKEL.		
MS20W23G30	30µ"GOLD PLATING OVER NICKEL.		

QUANTITY	PART NUMBER	DESCRIPTION		ITEM
MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED	SIGNATURES	DATE		
1) All dimensions are in metric(mm).	DRAWN:	BEN	JULY-1-2014	
2) Tolerances are as follows:	CHECKED:			
1 PL DEC ± 0.30 Fractions $\pm 1/64$	ENGINEER:			
2 PL DEC ± 0.15 Angles $\pm 1^\circ$	APPROVAL:			
3 PL DEC ± 0.08	CUSTOMER:			
3) Note reference = 	THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
MATERIAL SPECIFICATIONS:	PROCESS SPECIFICATIONS:			
NEXT ASS'Y:	SCALE: NONE			
SIZE: B	TYPE: C-	DWG NO: MS20W23XX	REVISION: B1	SHEET 1 OF 1

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

ECO-MATE, SOCKET CONTACT
MACHINE, 22-20AWG, SIZE 20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS20W23G5](#)