




- NOTES: (UNLESS OTHERWISE SPECIFIED)
- MATERIAL:
 - 1.1 CONTACT BODY: COPPER ALLOY.
 - 1.2 POSITIONING CLIP: COPPER ALLOY.
 - 1.3 CROWN SPRING CONTACT: COPPER ALLOY.
 - SPECIFICATIONS:
 - 2.1 CURRENT RATING: 13A(MAX).
 - 2.2 TERMINATION TYPE: CRIMPING.
 - 2.3 WIRE RANGE: 24~26AWG AND 28AWG.
 - SUITABLE SOCKET TYPE: MP24M23xx.
 - RoHS COMPLIANT.
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

B4

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B2	-	RELEASED DRAWING	JUN-19-2014	BEN	TOMMY
B3	-	Update drawing	Jun-21-18	Flan	Tommy
B4	-	Update drawing	Sep-21-18	Blink	Tommy

P/N	CONTACT PLATING(MATING AREA)
MS24M23T	TIN PLATING OVER NICKEL.
MS24M23S	SILVER PLATING OVER NICKEL.
MS24M23F	GOLD FLASH PLATING OVER NICKEL.
MS24M23G5	5µ"GOLD PLATING OVER NICKEL.
MS24M23G10	10µ"GOLD PLATING OVER NICKEL.
MS24M23G15	15µ"GOLD PLATING OVER NICKEL.
MS24M23G30	30µ"GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = 		SIGNATURES DATE DRAWN: Blink Sep-21-18 CHECKED: Tod Sep-21-18 ENGINEER: APPROVAL: Tommy Sep-21-18 CUSTOMER: THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
MATERIAL SPECIFICATIONS:		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
PROCESS SPECIFICATIONS:		ECO-MATE, SOCKET CONTACT, MACHINE, 24-28AWG, SIZE 16	
NEXT ASSY:		SIZE TYPE DWG NO. B C- MS24M23xx	REVISION B4
		SCALE NONE	SHEET 1 OF 1

TITLE: ECO-MATE SOCKET CONTACT MACHINE, 24-28AWG, SIZE 16
DWG NO: MS24M23xx
REV: B4
SH: 1
OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS24M23G30](#)