



		2	3	4	5	6	7	8																																																						
		(PG9) 13.6 ^{+0.1} 15.4±0.1 Recommended Panel Cut-Out		(M16*1.5) 13.6 ^{+0.1} 16.1±0.1 Recommended Panel Cut-Out		<table><tr><td>REV.</td><td>ECN NO.</td><td>DATE</td><td>SIGN</td><td>DESCRIPTION</td></tr><tr><td>B</td><td>LEN1580043~044</td><td>2015/07/26</td><td>Yulong_wang</td><td>Change to Share Drawing.</td></tr><tr><td>C</td><td>LEN1690066~067</td><td>2016/09/06</td><td>Yulong_wang</td><td>Add 3, 4 Pin & IP69K.</td></tr></table>			REV.	ECN NO.	DATE	SIGN	DESCRIPTION	B	LEN1580043~044	2015/07/26	Yulong_wang	Change to Share Drawing.	C	LEN1690066~067	2016/09/06	Yulong_wang	Add 3, 4 Pin & IP69K.																																							
REV.	ECN NO.	DATE	SIGN	DESCRIPTION																																																										
B	LEN1580043~044	2015/07/26	Yulong_wang	Change to Share Drawing.																																																										
C	LEN1690066~067	2016/09/06	Yulong_wang	Add 3, 4 Pin & IP69K.																																																										
				Note: * Important Dimension. * Waterproof Rate: IP68, IP69K. * Housing: Nylon+GF, Black. * Male Pin: Copper Alloy, Gold Plated. * Shield: Zinc Alloy, Nickel Plated. * Ground Pin: Copper Alloy, Gold Plated. * Screw Nut: Zinc Alloy, Nickel Plated. * Panel O-Ring: Viton, Black. * Rated Voltage: 3 & 4Pin 250V dc. or ac. 5Pin 60V dc. or ac. * Rated Current: 4A * Operating Temperature: -40~+105°C * For Panel Thickness Max 4.5mm. * Recommended Nut Torque: 4-6 Kgf.cm.																																																										
				Pin Assignment Front View																																																										
				<table><tr><td>UNIT:mm</td><td></td><td colspan="3">TITLE M12 B-Code Male Conn. PCB Type Shielded</td><td colspan="2">ITEM NO</td><td>DRAWN BY Yulong_wang</td><td>DATE 2016-09-06</td></tr><tr><td>TOLERANCE</td><td></td><td>SCALE 3:2</td><td>SIZE A4</td><td>SHEET 1 OF 2</td><td colspan="2">DWG NO MSBS-XXPMMP-SF8XXX</td><td>CHECKED BY Jinhai</td><td>DATE 2016-09-06</td></tr><tr><td>.X ±0.25</td><td></td><td>REV. C</td><td>WC-REV. A.5</td><td> Inspection item</td><td colspan="2">CUSTOMER ALTW</td><td>APPROVED BY Jerry</td><td>DATE 2016-09-06</td></tr><tr><td>.XX ±0.1</td><td></td><td colspan="3"></td><td colspan="2"></td><td></td><td></td></tr><tr><td>.XXX ±0.05</td><td></td><td colspan="3"></td><td colspan="2"></td><td></td><td></td></tr><tr><td>ANGLES ±1°</td><td></td><td colspan="3"></td><td colspan="2"></td><td></td><td></td></tr></table>					UNIT:mm		TITLE M12 B-Code Male Conn. PCB Type Shielded			ITEM NO		DRAWN BY Yulong_wang	DATE 2016-09-06	TOLERANCE		SCALE 3:2	SIZE A4	SHEET 1 OF 2	DWG NO MSBS-XXPMMP-SF8XXX		CHECKED BY Jinhai	DATE 2016-09-06	.X ±0.25		REV. C	WC-REV. A.5	Inspection item	CUSTOMER ALTW		APPROVED BY Jerry	DATE 2016-09-06	.XX ±0.1									.XXX ±0.05									ANGLES ±1°								
UNIT:mm		TITLE M12 B-Code Male Conn. PCB Type Shielded			ITEM NO		DRAWN BY Yulong_wang	DATE 2016-09-06																																																						
TOLERANCE		SCALE 3:2	SIZE A4	SHEET 1 OF 2	DWG NO MSBS-XXPMMP-SF8XXX		CHECKED BY Jinhai	DATE 2016-09-06																																																						
.X ±0.25		REV. C	WC-REV. A.5	Inspection item	CUSTOMER ALTW		APPROVED BY Jerry	DATE 2016-09-06																																																						
.XX ±0.1																																																														
.XXX ±0.05																																																														
ANGLES ±1°																																																														
				Amphenol LTW 安費諾亮泰企業股份有限公司																																																										
				8 FMW10702-01-02A1																																																										

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



M SBS - XX P M M P - S F 8 XXX

SBS:B-Code Shielded

03:3Pin

04:4Pin

05:5Pin

P:Panel(板端)

M:Male Connector(公座)

M:Male Pin(公Pin)

001:PG9


002:M16*1.5

8:IP68/69K(防水等級68/69K)

F:Front Fasten(前鎖式/Enclosure Rear Mount)

S:Screw(螺紋式)

P:PCB THT/DIP Type(180°基板插件式)



UNIT:mm		 	TITLE M12 B-Code Male Conn. PCB Type Shielded			ITEM NO		DRAWN BY Yulong-wang		DATE 2016-09-06	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			SCALE 3:2	SIZE A4	SHEET 2 OF 2	DWG NO MSBS-XXPMMP-SF8XXX		CHECKED BY Jinhai		DATE 2016-09-06	
			REV. C	WC-REV. A.3	QC: Inspection item	CUSTOMER ALTW		APPROVED BY Jerry		DATE 2016-09-06	
		2		3		4		5		6	
										7	
										8 FMM10702-01-02A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSBS-05PMMP-SF8001](#) [MSBS-05PMMP-SF8002](#)