



Technical drawing of a mechanical part showing dimensions and tolerances. The drawing includes a side view and a cross-sectional view. Dimensions are given in millimeters (mm) with tolerances in brackets.

- Top horizontal dimension: $\varnothing 18 \begin{smallmatrix} +0,1 \\ 0 \end{smallmatrix}$ [709 $\begin{smallmatrix} +0,05 \\ 0 \end{smallmatrix}$]
- Left vertical dimension: $10,1 \begin{smallmatrix} +0,1 \\ 0 \end{smallmatrix}$ [396 $\begin{smallmatrix} +0,05 \\ 0 \end{smallmatrix}$]
- Bottom left horizontal dimension: $2,8 \begin{smallmatrix} +0,1 \\ 0 \end{smallmatrix}$ [11 $\begin{smallmatrix} +0,05 \\ 0 \end{smallmatrix}$]
- Bottom right horizontal dimension: max 3,5 [138]

C
$$F$$
 E 6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T3263-420](#)