



Technical drawing of a mechanical part showing dimensions and tolerances. The drawing includes a side view and a cross-sectional view. Dimensions are given in millimeters (mm) with tolerances in brackets.

- Top horizontal dimension:  $\varnothing 18 \begin{smallmatrix} +0,1 \\ 0 \end{smallmatrix}$  [709  $\begin{smallmatrix} +0,05 \\ 0 \end{smallmatrix}$ ]
- Left vertical dimension:  $10,1 \begin{smallmatrix} +0,1 \\ 0 \end{smallmatrix}$  [396  $\begin{smallmatrix} +0,05 \\ 0 \end{smallmatrix}$ ]
- Bottom left horizontal dimension:  $2,8 \begin{smallmatrix} +0,1 \\ 0 \end{smallmatrix}$  [11  $\begin{smallmatrix} +0,05 \\ 0 \end{smallmatrix}$ ]
- Bottom right horizontal dimension: max 3,5 [138]

C
$$F$$
 $E$ 6

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T3303-420](#)