


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

INDUSTRIAL@AMPHENOL
TRUSTED GLOBALLY



Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a
Contact arrangement	IEC 60130-9 ⁿ	yes		no	yes		no	yes		no			
Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		60 V (32 V)	
Rated voltage	UL 1977	250V								60V			
Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)					
Pollution degree ²⁾	IEC 60664-1	1 (2)											
Installation category	IEC 60664-1	I											
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600											
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C						3A/+40°C			
Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ³⁾											
Contact resistance	IEC 60512-2-1	<5mOhm											
Climatic category	IEC 60668-1	40 / 100 / 56											
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F											
IP degree	IEC 60529	IP 40											
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N
mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles											
housing material		brass and / or zinc die cast, nickel plated or thermoplast											
dielectric material		thermoplastic											
contacts		silver or gold plated											
termination technique		solder											
wire gauge		≤0,5mm ² / 20 AWG								≤0,35mm ² / 22 AWG			
flamability		UL 94 V0											
locking system		metal screw coupling; tightening torque 0,7 - 1,5 Nm											

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.

All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	19 (19-a)	Ag	T 3691 001 U
		Au	T 3691 018 U
	14 (14-b)	Ag	T 3671 001 U
		Au	T 3671 018 U
	14 (14-a)	Ag	T 3651 001 U
		Au	T 3651 000 U
	12 (12-a)	Ag	T 3636 001 U
		Au	T 3636 000 U
	8 (08-a)	Ag	T 3505 001 U
		Au	T 3505 018 U
	7 (07-b)	Ag	T 3485 001 U
		Au	T 3485 018 U
	7 (07-a)	Ag	T 3476 001 U
		Au	T 3476 018 U
	6 (6-a)	Ag	T 3401 001 U
		Au	T 3401 018 U
	5 (05-b)	Ag	T 3361 010 U
		Au	T 3357 018 U
	5 (05-a)	Ag	T 3361 001 U
		Au	T 3361 018 U
	4 (04-a)	Ag	T 3301 001 U
		Au	T 3301 018 U
	3 (03-a)	Ag	T 3261 001 U
		Au	T 3261 018 U
	2 (Pin 1+3)	Ag	T 3201 001 U
		Au	T 3201 018 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. DIN EN 61076-2-106)	contact plating	Part number

Gewicht (errechnet) / Calc WT: 29,13 g				Zul. Abw./Tolerances: ISO 2768-c		Maßstab / Scale: 2:1		A3		
Prüfmaß / Testdimension						CUSTOMER DRAWING				
Teileindex / Partindexnumber:										
Bagatelle change: 23.02.2021 MCARLE				DIN / ISO 13715		Female cable connector Cable diameter 4-6mm				
				Drawn	MCARLE					
				Status	Released					
				Gepr.	10.02.2021					
				Checked	MBERTSCH	M DA T 3XXX 001+010+018 U				
				Amphenol Tuchel Industrial GmbH						
01	202000083	05.02.2021	MCARL			Blatt/ Sheet 1				
Index	Änderung/ Description	Datum/ Date	Name			1 Bl.				
						Ers. f. / Replacement for :				

FAI2020-004450
NXM-V01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T3401-018](#)