



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
01	-	TECHNICAL DATA SHEET RELEASE	27APR17	TZ	TZ



SHIELDED: GREY OVERMOLD



TECHNICAL DATA:

1) MATERIALS:

COUPLING NUT: MACHINED STEEL, NICKEL PLATED
INSULATION INSERT: THERMOPLASTIC, UL 94/V-0
CONTACT: GOLD FLASH PLATING OVER COPPER ALLOY
OVERMOLD MATERIAL: THERMOPLASTIC
CONDUCTOR RATING: TC-ER PER UL 1277
CONDUCTOR INSULATION: XLPE
NUMBER OF CONDUCTORS: (4) 12AWG

2) ELECTRICAL DATA:

CURRENT (MAX): 25A (2237) 29A (2238)
VOLTAGE (MAX): 600V AC/DC
INSULATION RESISTANCE (MIN): 5000M OHMS
DIELECTRIC TEST VOLTAGE: 2200V

3) MECHANICAL DATA:

TEMPERATURE RANGE: -40°C TO 90°C
PROTECTION: IP67 (MATED CONDITION)
MATING CYCLES: >500
VIBRATION RESISTANCE PER MIL-STD-202 METHOD 204
THERMAL SHOCK PER MIL-STD-202 METHOD 207
48 HOUR SALT SPRAY PER MIL-STD-202 METHOD 101

4) RoHS COMPLIANT

5) UL 2237 LISTED ASSEMBLY

UL FILE NUMBERS: E339703, 224856



PART NUMBER		DESCRIPTION		ITEM		
QUANTITY		MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE		
1) All dimensions are in metric(mm).		DRAWN:	TZ	28APR17		
2) Tolerances are as follows:		CHECKED:	TZ	28APR17		
1 PL DEC ±0.30		ENGINEER:	TZ			
2 PL DEC ±0.15		APPROVAL:	TZ	28APR17		
3 PL DEC ±0.08		CUSTOMER:				
3) Note reference = 		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.				
MATERIAL SPECIFICATIONS:		MALE STRAIGHT, FEMALE STRAIGHT, SHLD POWER, M29, 12AWG, CABLE ASSY				
PROCESS SPECIFICATIONS:						
NEXT ASSY:		SIZE	TYPE	DWG NO:	REVISION	
			C-	P31387-M()	01	
		SCALE:	NONE	C-P31387	SHEET 1	OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[P31387-M7](#)