





REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
C	PROPOSAL	AUG 01/05	L.CHAN
D	UPDATE DRAWINGS	MAY 23/17	L.CHAN



RECOMMENDED PANEL CUTOUT

MATERIALS:

HOUSING: ENGINEERING THERMOPLASTIC  
FLAMMABILITY RATING UL 94V-0  
COLOUR: BLACK.

CONTACTS: PHOSPHOR BRONZE


PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES  
SEE AMPHENOL PART NUMBER FOR DETAIL.  
50U" MIN. NICKEL OVERALL  
GOLD FLASH ON CONTACT TAILS.

RECOMMENDED SOLDERING TEMPERATURE:  
WAVE SOLDERING AT 260°C MAXIMUM FOR 5 SEC MAXIMUM.



AMPHENOL PART NO: RJE08-1AA-0X10

GOLD PLATING:  
1 = 6 μ"  
2 = 15 μ"  
3 = 30 μ"  
4 = 50 μ"



RECOMMENDED P.C.B. LAYOUT  
(COMPONENT SIDE OF BOARD)  
TOLERANCE: ±0.05 (TOP VIEW)

UNLESS SPECIFIED OTHERWISE		DRAWN PAUL WANG	DATE MAR04/05	Amphenol Canada Corp.	
PRIMARY UNITS	INCH	CHECKED L.CHAN	DATE MAR04/05	www.amphenolcanada.com	
SECONDARY	MILLIMETER	M.E. APP'D		TITLE	
REFERENCE IN PARENTHESES		Q.A. APP'D		RJ45 CONNECTOR, TOP ENTRY	
GENERAL TOLERANCES		DWG APPR.		10P 10C, P.C.B. MOUNT,	
1 DECIMAL PLACE	±0.025	ENG. REL. NO.		WITHOUT SHIELD-ROHS COMPLIANT	
2 DECIMAL PLACES	±0.020	REF.		DWG. NO.	
3 DECIMAL PLACES	±0.015	THIRD ANGLE PROJECTION		P-RJE08-1AA-0X10	
ANGULAR DEGREES	±1.0°	DO NOT SCALE DRAWING		REV D	
		CODE ID NO. 03554	DWG SIZE: C	SCALE: N/A	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJE08-1AA-0110H](#) [RJE08-1AA-0210H](#) [RJE08-1AA-0310H](#) [RJE08-1AA-0410H](#)