


Copied from this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.




Valid for contact arrangement:
05b, 07b, 08a, 12a, 14a

Valid for contact arrangement:
03a, 04a, 05a, 06a, 07a

Panel cutout M 1:1



shown with ring nut



Number of contacts	Standard	3	4	5	5S	6	7	7	8	12	14
Contact arrangement	DIN EN 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a
Contact arrangement	IEC 60130-9 ¹⁾			-			-			-	
Rated voltage	IEC 60664-1	300 V (100 V)	300 V (63 V)	100 V (32 V)	300 V (63 V)	100 V (32 V)	150 V (32 V)				
Rated voltage	UL 1977			250 V							
Rated impulse withstand voltage	IEC 60664-1	1500 V (840 V)	1200 V (500 V)	1500 V (840 V)	1200 V (500 V)						
Pollution degree	IEC 60664-1			1 (2)							
Installation category	IEC 60664-1			I							
Insulation group	IEC 60664-1			II, 400 ≤ CTI < 600							
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C/+104°F							
Insulation resistance	IEC 60512-3-1			>10 ¹⁰ Ohm ²⁾							
Contact resistance	IEC 60512-2-1			<5m Ohm							
Climatic category	IEC 60668-1			40 / 100 / 56							
Temperatur range	IEC 60668-1			-40°C...+100°C / -40°F...+212°F							
IP degree	IEC 60529			IP 40							
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	50N	55N	60N	50N			
Mechanical operation	IEC 60512-9-1			silver ≥500 mating cycles gold ≥1000 mating cycles							
Housing material				brass or zinc die cast nickel plated or thermoplast							
Dielectric material				thermoplastic							
Contacts				silver or gold plated, please order contacts separately acc. to drawing M-N 02 015 00XX X (3-8pol) or M-N 02 010 0157 X U (12-14pol)							
Termination technique				crimp							
Wire gauge				2-6 pol (exclusive 5S): 0,09-1,0mm ² / 28-18 AWG 5S, 7, 7S, 8pol: 0,09-0,75mm ² / 28-20 AWG							
Flamability				UL 94 V0							
locking system				bayonet locking outside (mateable with locking inside)							

¹⁾ Edition 2000-05

²⁾ under operating conditions >10⁸ Ohm

All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties. Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground. Parts according to directive 2002/95/EG (RoHS).

	14 (14-a)	T 3647 150 U	T 3647 159 U
	12 (12-a)	T 3627 150 U	T 3627 159 U
	8 (08-a)	T 3527 150 U	T 3527 159 U
	7 (07-b)	T 3447 150 U	T 3447 159 U
	7 (07-a)	T 3437 150 U	T 3437 159 U
	6 (06-a)	T 3427 150 U	T 3427 159 U
	5 (05-b)	T 3397 150 U	T 3397 159 U
	5 (05-a)	T 3377 150 U	T 3377 159 U
	4 (04-a)	T 3327 150 U	T 3327 159 U
	3 (03-a)	T 3277 150 U	T 3277 159 U
Contact arrangement View on mating side	Number of contacts	type-number-crimp with ring nut	type-number-crimp with hex nut SW20
dimension of nut			

Gewicht (errechnet) / Calc WT:	Zul. Abw./Tolerances:	Maßstab / Scale: 2:1;1:1	A3	
Prüfmaß / Testdimension	ISO 2768-c	CUSTOMER DRAWING		
Teileindex / Partindexnumber:				
Bagatelle change:				
	Gez. 28.04.2020	Gerätedose female receptacle		
	Drawn MCARLE			
	Status Released			
	Gepr. 30.04.2020			
	Checked MGRIMM			
	Amphenol Tuchel Industrial GmbH			
01 202000001 30.04.2020 MCARLE		M NB T 3XX7 15X U	Blatt / Sheet 1	
Index Änderungs / Description Datum / Date Name		Ers. f. / Replacement for: M-NB T 3XX7 150 Rev01		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T3527-150](#)