





N 01 016-0011 (2)/(102)	Cu/Ni2 Au0,5	0.14-0.50 mm ² AWG 26-20
N 01 016-0011 (1)/(101)	Cu/Ni0,5 Ag2 pas	
N 01 016-0004 (2)/(102)	Cu/Ni2 Au0,5	0.50-1.5 mm ² AWG 20-16
N 01 016-0004 (1)/(101)	Cu/Ni0,5 Ag2 pas	
Typ-Nr. / Type-No.	Oberfläche im Kontaktbereich Plating in contact area	Anschlussquerschnitt terminal cross-section

HN 01 016-00XX (X)	Band 2000 St. Rechtseinlauf / Reel 2000 pcs. infeed right
TN 01 016-00XX (X)	Band 2000 St. Linkseinlauf / Reel 2000 pcs. infeed left
ZN 01 016-00XX (X)	Band 200 St. / Reel 200 pcs.
VN 01 016-00XX (X)	Einzelkontakt 100 St. / Single contact 100 pcs.
Bestell-Nr. / Part-No.	Verpackungsform / Packaging

Masse (errechnet)/Calc WT:			9	Zul. Abw./Tolerances:		Maßstab/Scale 5:1		A3	
 Prüfmaß/Testdimension					 DIN/ISO 13715		CUSTOMER DRAWING		
Teileindex Part index number									
				06	Datum/Date	Name	Stiftkontakt pin contact		
				Gez. Drawn	04.05	N.Sifer			
				Gepr.					
				Checked					
				Amphenol-Tuchel Electronics GmbH			M	N 01 016 00XX (X)	Blatt/Sheet 1
01	201000049	04.05.10	Si.						1 Bl.
Index	Änderung/Description	Datum/Date	Name	Ers. f./Replacement for:					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VN01 016 0004 2](#) [VN01-016-0011-2](#) [VN01 016 0011 1](#) [VN01 016 0004 1](#)