





RECOMMENDED PCB LAYOUT

Poles	Dim L	Dim B	Dim C
2×2-2×5p	±0.15	±0.15	±0.15
2×6-2×10p	±0.20	±0.20	±0.20
2×11-2×15p	±0.25	±0.25	±0.25
2×16-2×20p	±0.30	±0.30	±0.30
2×21-2×24p	±0.35	±0.35	±0.35

N = Number of poles
 Dim L=(N-1)×3.81+14.2
 Dim B=(N-1)×3.81
 Dim C=(N-1)×3.81+9.0



SECTION A-A

SIGN	DATE	DESCRIPTION	APPROVER
△	1/30'07	Soldering temperature changed from 245° to 250°	Tony
△	04/08'09	The current rating and operating temperature are changed	Jacke
△	04/08'09	Add UL standard	Jacke
△	2009.10.10	The design is changed from the round hole to hexagonal hole.	Jacke
△	07/05'11	Remove the "T" shape	Aaron
△	04/26'12	The Dimension Dim C is added	Chen Bo
△	04/26'12	Flange nut is changed	Chen Bo
△	04/26'12	Add the cutaway view	Chen Bo
△	04/26'12	The material is changed from Brass to Copper	Chen Bo
△	11/20'12	update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Male Contact pin: Copper, Tin plated
- Item ② Terminal (housing): Thermoplastic (UL94V-0)
- Item ③ Terminal (cover): Thermoplastic (UL94V-0)
- Item ④ With flange nut: Brass M2.5

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: △

VO xx 3 2 x 0 xxxx G

No. OF POLES
 04: 2×2 POLES
 :
 48: 2×24 POLES

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G: RoHS compliant (lead<4%)
 In copper Alloy
 0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VO-3.81 Series 2×2P-2×24P Vertical (With flange)						
PART NO.	VOxx32x0xxxxG			DWG NO.	8VO0104		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Chen Bo 11/20'12	Chen Bo 04/26'12		X. ±0.50		
					X.X ±0.30		
					X.XX ±0.10		
					X° ±1°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VO0432500000G</u>	<u>VO0632500000G</u>	<u>VO0832500000G</u>	<u>VO1032500000G</u>	<u>VO1232500000G</u>	<u>VO1432500000G</u>
<u>VO1632500000G</u>	<u>VO1832500000G</u>	<u>VO2032500000G</u>	<u>VO2232500000G</u>	<u>VO2432500000G</u>	<u>VO2632500000G</u>
<u>VO2832500000G</u>	<u>VO3032500000G</u>	<u>VO3232500000G</u>	<u>VO3432500000G</u>	<u>VO3632500000G</u>	<u>VO3832500000G</u>
<u>VO4032500000G</u>	<u>VO4232500000G</u>	<u>VO4432500000G</u>	<u>VO4632500000G</u>	<u>VO4832500000G</u>	