









Dimension

Dim A	(N-1)×7.62+5.6
Dim B	(N-1)×7.62

N= Number of poles

Poles	Tolerance
2P-7P	±0.25
8P-12P	±0.30
13P-16P	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	2008.6.19	The dimension changed from 26.00mm to 26.25mm	Jacke
△	2010.03.12	Add the 2p mark	Jacke
△	2010.04.20	The dimension is revised.	Jacke
△	2010.05.17	The design is changed	Jacke
△	2011.08.08	The mark "7.62" is added	Aaron
△	2011.08.08	The dimension 2.6 is added	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item a Terminal up body:Thermoplastic (UL94V-0)
- Item b Terminal down body:Thermoplastic (UL94V-0)
- Item c Terminal screw:Steel Zinc plating "-" slot type
- Item d Clamp:Brass, Ni plated
- Item e Female contact:PhBz (CuSn) Tin plated

Electrical cULus/TUV

- Voltage rating: 300VAC/750VAC
- Current rating: 15A/15A
- Wire range:0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5 Lb-In 0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- △ Withstanding Voltage: 1.6KV/6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus TUV
- Critical dimension: ▽

TS xx 01 x A xxxx G

	Color	RoHS
02 2 CONTACTS	0 Black (RAL9005)	Pb<40,000ppm
03 3 CONTACTS	2 Red (RAL3001/D)	
... ..	3 Orange(RAL2011/P)	
16 16 CONTACTS	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TS 7.62 Series 2P-16P (Without flange) hook on entry side				DWG NO.		8TS0501	
PART NO.		TSxx01xAxxxxG			CUST NO.				
APPROVED		CHECKED	DESIGNED	DRAWN			Tolerance		
Shi Jun 2011.08.09		Aaron 2011.08.08	Jacke 2010.05.17			UNIT: mm		X.	±0.50
						SCALE: NONE		X.X	±0.30
						REV: G		X.XX	±0.10
				SHEET: 01/01				X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TS02015A0000G</u>	<u>TS03015A0000G</u>	<u>TS04015A0000G</u>	<u>TS05015A0000G</u>	<u>TS06015A0000G</u>	<u>TS07015A0000G</u>
<u>TS08015A0000G</u>	<u>TS09015A0000G</u>	<u>TS10015A0000G</u>	<u>TS11015A0000G</u>	<u>TS12015A0000G</u>	<u>TS13015A0000G</u>
<u>TS14015A0000G</u>	<u>TS15015A0000G</u>	<u>TS16015A0000G</u>	<u>TS09010A0000G</u>	<u>TS12018A0000G</u>	<u>TS10010A0000G</u>
<u>TS14010A0000G</u>	<u>TS16018A0000G</u>	<u>TS12010A0000G</u>	<u>TS14018A0000G</u>	<u>TS07010A0000G</u>	<u>TS15018A0000G</u>
<u>TS02018A0000G</u>	<u>TS15010A0000G</u>	<u>TS16010A0000G</u>	<u>TS04010A0000G</u>	<u>TS02010A0000G</u>	<u>TS02012A0000G</u>
<u>TS04018A0000G</u>	<u>TS03010A0000G</u>	<u>TS05018A0000G</u>	<u>TS10018A0000G</u>	<u>TS05010A0000G</u>	<u>TS08018A0000G</u>
<u>TS03018A0000G</u>	<u>TS06010A0000G</u>	<u>TS08010A0000G</u>	<u>TS09018A0000G</u>	<u>TS07018A0000G</u>	<u>TS11018A0000G</u>
<u>TS13010A0000G</u>	<u>TS11010A0000G</u>	<u>TS13018A0000G</u>	<u>TS06018A0000G</u>		